


ORDER NO.	WOODHEAD NO.	COLOR
130141-0031	1547	YELLOW
130141-0032	1547BLK	BLACK








* FOR SCREW TORQUE, SEE ASSEMBLY INSTRUCTIONS

ITEM NO.	DESCRIPTIONS	MATERIAL	QTY.
1	CLIP ASSEMBLY	BRASS, NICKEL PLATED	3
2	RETAINING SCREWS	STAINLESS STEEL	3
3	TERMINAL SCREWS/CLAMP ASSEMBLY	BRASS, ZINC PLATED	3
4	INSERT	NYLON	1
5	TERMINAL COVER	POLYCARBONATE	1
6	CONNECTOR HUSK	RUBBER	1
7	CLAMP SUPPORT	NYLON	1
8	CLAMP CORD MALE	NYLON	1
9	CLAMP CORD INSERT	NYLON	1
10	CLAMP CORD FEMALE	NYLON	1
11	RETAINING SCREWS	STEEL ZINC PLATED	2

WIRING TERMINATION



DOCUMENT STATUS	P1	RELEASE DATE	2020/09/02 23:00:14

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SYMBOLS: = 0 (E) = 0 (E) = 0 (E) = 0 (▼) = 0 (E) = 0 (☒) = 0 (■) = 0 (▽) = 0

DIMENSION UNITS: INCH/MM — SCALE: NTS

GENERAL TOLERANCES (UNLESS SPECIFIED)

	MM	INCH
4 PLACES	±	±
3 PLACES	±	± 0.005
2 PLACES	± 0.13	± 0.01
1 PLACE	± 0.25	± 0.02
0 PLACES	±	±
ANGULAR TOL	± °	

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC: NEW RELEASE

EC NO: 643354
DRWN: VHANDI 2019/06/14
CHK'D: DNGUYEN62 2020/06/30
APPR: HKNEELAND 2020/09/02

INITIAL REVISION:
DRWN: VHANDI 2019/06/14
APPR: HKNEELAND 2020/09/02

THIRD ANGLE PROJECTION | DRAWING: B-SIZE | SERIES: 130141

molex

SUPER-SAFEWAY CONN NEMA 5-15 2P3W

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
1301410031	PSD	000	A

MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
SEE TABLE	GENERAL MARKET	1 OF 1

FORMAT: Eng-lega-master-tb-prod-B
REVISION: D
DATE: 2018/01/18