



[CLOCK IN](#)

[REGISTER](#)

FIND YOUR LOCAL STOCKIST: go

SEARCH go

[HOME](#)

[FIND A TOOL](#)

[PROMOTIONS](#)

[KNOWLEDGE HUB](#)

[NEWS](#)

[CONTACT US](#)

SHARE

You are here: [Home](#) » [Categories](#) » [Bit Adaptor](#) » FatMax® Bit Adaptor

FIND A TOOL

FATMAX® BIT ADAPTOR

Rating:
 18 Ratings [Review now >>>](#)

[Measuring, Levelling and Layout](#) (1165)

[Lasers, Electronic Devices and Torches](#) (397)

[Knives and Blades](#) (2324)

Screwdrivers

[FatMax® XL™ Screwdriver Sets](#) (158)

[FatMax® XL™ Insulated Screwdrivers](#) (86)

[FatMax Screwdrivers](#) (143)

[FatMax Insulated Screwdrivers](#) (58)

[Bit Adaptor](#) (18)

[FatMax Screwdriver Sets](#) (143)

[Cushion Grip Screwdrivers](#) (252)

[Cushion Grip Screwdriver Sets](#) (264)

[Mains Tester](#) (37)

[Stanley Screwdriver Sets](#) (102)

[XL Demolition Driver](#) (17)

[Multibit Ratchets and Precision](#) (259)

[Screwdriver Bits](#) (24)

[Drills](#) (13)

[Saws](#) (835)

[Chisels, Planes and Surform](#) (570)

[Demolition, Hammers and Chisels](#) (554)

[Clamps and Pliers](#) (396)

[Sockets, Spanners and Wrenches](#) (525)

[Stapling, Riveting and Gluing](#) (316)

[Tool Storage](#) (1361)

[>>> VIEW ALL REVIEWS](#)

[Review this product](#)

[VIEW LARGER](#)



[DESCRIPTION](#)

[WRITE REVIEW](#)

[READ REVIEWS](#)

FATMAX® BIT ADAPTOR

[Like](#)

Sign Up to see what your friends like.

Features and Benefits:

Large diameter handle offers great torque needed for driving wood screws

Soft grip handle – perfect combination of great grip plus reduces fatigue

Smooth domed end for fast spinning action – speed and comfort

Chrome vanadium steel bar allows for high torque and reduces the chance of tip breakage

Handle moulded direct to bar virtually unbreakable bond. Highly reliable and providing an extra long life

Colour coded ends make it easy to identify the correct screw driver for each screw type

	0-65-490	1-65-490
Length in mm	125	125
Width tip in inches	1/4	1/4
Ex VAT Price £	6.74	6.74