

CABLE ASSEMBLIES

HDTV TRANSMISSION LINE NETWORK PRODUCT SOLUTIONS - ALL TRUE 75 OHM


For over 35 years, Trompeter has been producing high quality cable assemblies, and currently provides over 500,000 different configurations using a broad range of RF connectors and cable types. We stock a variety of components for camera, RGB, S-Video, audio, and many other applications.

Capabilities

Trompeter can provide patching products with special marking (ID sleeves/tags, hot stamping, colored cable jacket, etc). Trompeter offers 24-48 hour turn-around on many standard products with full capabilities for sustained volume delivery. Deliveries can be adjusted to meet your specific needs.

Trompeter's assemblies are 100% electrically tested for continuity, shorts, and Hi-Pot. (Voltage Standing Wave Ratio (VSWR), Isolation Resistance (IR), Insertion/Return Loss test capabilities, SPC data available on request.

Trompeter's coax patch cords and cable assemblies are of the highest quality and can be ordered in any length. Trompeter normally stocks popular lengths of 18", 24", 36", 48", 60" and 72".




WECO Video Patch Cords

Patch Plug to Patch Plug

75 Ohm WECO, .090" Center Pin

PCW-L-Z (Red, Black, Yellow, Green, Blue, Violet)

Specify color when ordering video patch cords. Replace "L" with length in inches (Most common lengths: 12", 18", 24", 36", and 48") Example: PCW-24-75RED - 24 inch Video Patch Cord, Red colored cable.




WECO Cable Assembly

UPL2000 BNC Plug to UPL2000 BNC Plug

Tool Crimp BNC 75 ohm

UPCYB-L-Z



WECO Cable Assembly

Patch Plug to BNC Plug

75 ohm WECO Center Pin .090"


75 ohm BNC **UPCWX-L-Z**



Mini-WECO Patch Cords:

PCMWB-(length in inches)

Broadcast mini-Weco 75 ohm patch plugs and 75 ohm cable for use with J314MW series patch jacks.



WECO Cable Assembly

Patch Cords: Triple Paralleling

Junction	Standard	Max Length	Part #
Molded	75 ohm WECO center pin .090"	14"	PCWS-L-75
Metal	75 ohm WECO center pin .090"	none	PCWSE-L-75

Request For Quotes...Please refer to the following guideline when requesting a quote:

1	2	3	4	5	6
Quantity	Connector 1	Cable	Connector 2	Length	Special Requirements
12	UPL2000-D5	Belden 7731A	UPL2000-D5	60"	none

- 1 Quantity
- 2 Connector 1.....Select from connectors in this catalog or call factory.
- 3 Cable.....Select from cables in this catalog or call factory.
- 4 Connector 2.....Select from connectors in this catalog or call factory.
- 5 Length.....In Inches
- 6 Write out any special marking, testing, bend relief, packaging, or other special requirements.

* Contact factory more information on other connector types and cables.
 "L" denotes the length in inches. "Z" denotes the impedance of the connecting cable.