Gigabit Network Switches

The NLHUB-505/NLHUB-588 are high performance gigabit switches capable of 10/100/1000Mbps auto negotiation operation. All ports support store & forward architecture and auto MDI/MDIX function. Offers easy installation and a cost effective SOHO solution.

Specification:

- 5 or 8 x Gigabit Ethernet ports Compliant with IEEE 802.3, IEEE 802.3u, IEEE 802.ab Supports IEEE 802.3x flow control for full duplex mode
- Supports back pressure for half duplex mode Supports full/half duplex in 10/100m mode
- Supports full duplex in 1000m mode
- Supports auto negotiation Supports store and forward
- Supports auto MDI/MDI-X

NLHUB-505 - 5 Port 10/100/1000 Ethernet Switch NLHUB-588 - 8 Port 10/100/1000 Ethernet Switch



10/100 Desktop Network Switches

The NLHUB-905A/NLHUB-908M are 5/8 port Ethernet switches. These products would be ideal at the heart of all home or small networking systems with its fast speeds of 10/100Mbps and its automatic MAC learning capabilities. Both have a wall mountable case so it is possible to attach to a wall or be placed on a convenient flat surface.

Specification:

- Complies with IEEE802.3, IEEE 802.3u standards.

- 5/8 port 10/100 Mbps Supports Auto-MDI/MDI-X. Supports IEEE 802.3x flow control for Full Duplex and Half Duplex modes.
- Supports MAC address auto-learning and auto-aging.
- Expandable by cascading more hubs together.
 LED indicators for monitoring power, link, activity.
- External power adaptor supplied.

NLHUB-905A - 5 Port 10/100 Ethernet Switch NLHUB-908M - 8 Port 10/100 Ethernet Switch



10/100 Rack Mount Network Switches

These products would be ideal at the heart of all networking systems with its fast speeds of 10/100Mbps and its automatic MAC learning capabilities. They come with a standard 1U 19-inch rack mountable steel case which enables an optimum number of ports while only taking up minimal space.

Specification:

- Complies with IEEE802.3, IEEE 802.3u standards.
- 16/24 port 10/100 Mbps
- Supports Auto-MDI/MDI-X.
- Supports IEEE 802.3x flow control for Full Duplex and Half Duplex modes.
- External power adaptor supplied.

NLHUB-916A - 16 Port 10/100 Ethernet Switch

• 17.5" Switch, bracket to fit 19" rack, 1U

NLHUB-916COMPACT - 16 Port 10/100 Ethernet Switch

• 11" Switch, bracket to fit 19" rack 1U

NLHUB-924A - 24 Port 10/100 Ethernet Switch

• 17.5" Switch, bracket to fit 19" rack, 1U

NLHUB-924COMPACT - 24 Port 10/100 Ethernet Switch

11 "Switch, bracket to fit 19" rack, 1U





sales@cablesdirect.co.uk