


DYMO®

practically genius

Digital Postal and Shipping Scales



Save time and money. Weigh any envelope or package for precise postage, every time.

With DYMO Postal Scales you can weigh envelopes and packages up to 10 kg – without a trip to the Post Office or mailroom. Compact size fits on any desk and stores in most desk drawers. Powered by three AAA batteries (not included) or USB cable when connected to a PC or Mac (M5 and M10 only).

All DYMO Postal scales have the following features:

- “Hold” feature locks weight display for 10 seconds after package is removed – convenient when large package blocks view of display
- Tare function – weigh items in a container minus weight of container
- Automatic shut-off when scale not in use – prolongs battery life

Scale features	M1	M2	M5	M10
Product number (SKU)	S0928980	S0928990	S0929000	S0929010
Maximum Weight	1 kg	2 kg	5 kg	10 kg
Weight display	0 kg 000 g	0 kg 000 g	0 kg 000 g	0 kg 000 g
Weight interval	1 g	1 g	2 g	2 g
Auto shut-off	✓	✓	✓	✓
Hold button	✓	✓	✓ + LED indicator	✓ + LED indicator
Tare button	✓	✓	✓	✓
USB connection	-	-	✓	✓
Power source (Batteries excluded)	3 x AAA Batteries	3 x AAA Batteries	USB cable or 3 x AAA Batteries	USB cable or 3 x AAA Batteries
Platform dimensions	15 cm x 15 cm	15 cm x 15 cm	20 cm x 20 cm	20 cm x 20 cm

Digital Postal Scales

1 kg



M1 Digital Postal Scale

- Up to 1 kg capacity
- Displays weight in 1 g increments
- Powered by 3 AAA batteries (not included)

2 kg



M2 Digital Postal Scale

- Up to 2 kg capacity
- Displays weight in 1 g increments
- Powered by 3 AAA batteries (not included)

Digital USB Postal Scales

5 kg



Windows® XP
Windows Vista®
Windows® 7

Mac OS® v10.4
and later

M5 Digital USB Postal Scale

- Up to 5 kg capacity
- Displays weight in 2 g increments
- Runs on USB power from computer or 3 AAA batteries (not included)

10 kg



Windows® XP
Windows Vista®
Windows® 7

Mac OS® v10.4
and later

M10 Digital USB Postal Scale

- Up to 10 kg capacity
- Displays weight in 2 g increments
- Runs on USB power from computer or 3 AAA batteries (not included)



Heavy-duty portable scales for packages up to 180 kg.

With DYMO® Portable Digital USB Shipping Scales you'll save time, money – and just maybe your back! Weigh packages up to 180 kg. Grab the built-in handle and carry the scale to heavy items – instead of lugging heavy items to the scale!

All DYMO® Shipping scales have the following features:

- 'Hold' feature locks weight display for 10 seconds after package is removed – convenient when large package blocks view of display
- Tare function – weigh items in a container minus weight of container
- Automatic shut-off when scale not in use – prolongs battery life
- Detachable LCD display for convenient hand-held or wall-mounted viewing
- Powered by AC adapter (included), 3 AAA batteries (not included) or USB cable (included) when connected to a PC or Mac



Portable Digital USB Shipping Scales

50 kg



USB



Windows® XP
Windows Vista®
Windows® 7



Mac OS® v10.4
and later

S50 Portable Digital USB Shipping Scale

- Up to 50 kg capacity
- Displays weight in 100 g increments
- Runs on USB power from computer, AC adapter (included) or 3 AAA batteries (not included)

100 kg



USB



Windows® XP
Windows Vista®
Windows® 7



Mac OS® v10.4
and later

S100 Portable Digital USB Shipping Scale

- Up to 100 kg capacity
- Displays weight in 100 g increments
- Runs on USB power from computer, AC adapter (included) or 3 AAA batteries (not included)

180 kg



USB



Windows® XP
Windows Vista®
Windows® 7



Mac OS® v10.4
and later

S180 Portable Digital USB Shipping Scale

- Up to 180 kg capacity
- Displays weight in 200 g increments
- Runs on USB power from computer, AC adapter (included) or 3 AAA batteries (not included)

Scale features	S50	S100	S180
Product number (SKU)	S0929020	S0929030	S0929040
Maximum Weight	50 kg	100 kg	180 kg
Weight display	0.0 kg	0.0 kg	0.0 kg
Weight interval	100 g	100 g	200 g
Auto shut-off	✓	✓	✓
Hold button	✓	✓	✓
Tare button	✓	✓	✓
USB connection	✓	✓	✓
Detachable display	✓	✓	✓
Power source (Batteries excluded)	USB cable, AC adapter or 3 x AAA Batteries	USB cable, AC adapter or 3 x AAA Batteries	USB cable, AC adapter or 3 x AAA Batteries
Platform dimensions	30 cm x 30 cm	30 cm x 30 cm	30 cm x 30 cm

Dealer:

Microsoft Windows®, Windows Vista®, the Windows® logo, Outlook® and Excel® are trademarks or registered trademarks of Microsoft Corporation. Mac® and Mac OS® are registered trademarks of Apple, Inc. All other trademarks are the property of their respective owners.

DYMO

A **NewellRubbermaid** Brand

Produced by:
DYMO bvba, Sint-Niklaas, Belgium
www.dymo.com © 2010 Sanford, L.P.
S0948510 10-0995