



Electronics

a vital part of your world

Find Answers:

Sunday, 23 October, 2005

CATALOG

Cross Reference

- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

Home

e-bulletin newsletter
SUBSCRIBE NOW!
 click here

Subminiature and Microminiature D Connectors

↳ Cable Clamps

AMP 207467-1 Active

Directive 2002/95/EC Compliant

RoHS Compliant

(Corporate P/N: 207467-1)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ➤ General Info ➤ Sales Info ➤ Assembly Subcontractors 	<ul style="list-style-type: none"> ➤ Pricing ➤ Product Availability 	<ul style="list-style-type: none"> ➤ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

Searchable Features:	
Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Processes:	Not relevant for lead free process
Product Type:	Cable Clamp
Cable Clamp Type:	Box and Lid
Cable Exit Angle:	Straight(180°)/90°
Cable Insulation Diameter (mm [in]):	4.06 [0.160]
Shell Size:	1
Shielded:	No
Screws and Retainer Clips:	Without
Grommets:	Without

Other Properties:	
Packaging Quantity:	50
Body Finish:	Textured
Cable Support Gate Material:	Thermoplastic
Cable Clamp Material:	Thermoplastic
Screw Material:	Steel
Screw Plating:	Zinc
Comment:	Cable diameter is adjustable by changing cable support gates. Use the flat side of cable support gates for discrete wire, and the semicircle side for jacketed cable. All parts are packaged unassembled.

Packaging Method:	Individual Kit
Thread Size:	None
Housing Material:	Thermoplastic
Housing Plating:	None

[Copyright and Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]

.