

Molex Kit BOM



KK-156, 3.96mm, 226 Pieces

Mfftr Part Number: 76650-3008

Included Parts	Description	Quantity
08-50-0106	3.96mm (.156") KK® terminal, Brass, 18-20 AWG, loose piece	50
09-50-8023	3.96mm (.156") Pitch KK® Crimp Terminal Housing, w/ locking ramp, w/ polarizing ribs, 02 ckts	10
09-50-8033	3.96mm (.156") Pitch KK® Crimp Terminal Housing, w/ locking ramp, w/ polarizing ribs, 03 ckts	10
09-50-8043	3.96mm (.156") Pitch KK® Crimp Terminal Housing, w/ locking ramp, w/ polarizing ribs, 04 ckts	10
09-50-8053	3.96mm (.156") Pitch KK® Crimp Terminal Housing, w/ locking ramp, w/ polarizing ribs, 05 ckts	5
09-50-8063	3.96mm (.156") Pitch KK® Crimp Terminal Housing, w/ locking ramp, w/ polarizing ribs, 06 ckts	5
09-50-8083	3.96mm (.156") Pitch KK® Crimp Terminal Housing, w/ locking ramp, w/ polarizing ribs, 08 ckts	5
09-50-8103	3.96mm (.156") Pitch KK® Crimp Terminal Housing, w/ locking ramp, w/ polarizing ribs, 10 ckts	5
26-60-4020	3.96mm (.156") Pitch KK® Solid Header, Vertical, Friction Lock, Polarised, Tin plated	10
26-60-4030	3.96mm (.156") Pitch KK® Solid Header, Vertical, Friction Lock, Polarised, Tin plated	10
26-60-4040	3.96mm (.156") Pitch KK® Solid Header, Vertical, Friction Lock, Polarised, Tin plated	10
26-60-4050	3.96mm (.156") Pitch KK® Solid Header, Vertical, Friction Lock, Polarised, Tin plated	5
26-60-4060	3.96mm (.156") Pitch KK® Solid Header, Vertical, Friction Lock, Polarised, Tin plated	5
26-60-4080	3.96mm (.156") Pitch KK® Solid Header, Vertical, Friction Lock, Polarised, Tin plated	5
26-60-4100	3.96mm (.156") Pitch KK® Solid Header, Vertical, Friction Lock, Polarised, Tin plated	5
26-60-5020	3.96mm (.156") Pitch KK® Solid Header, Right angle, Friction Lock, Polarised, Tin plated	10
26-60-5030	3.96mm (.156") Pitch KK® Solid Header, Right angle, Friction Lock, Polarised, Tin plated	10
26-60-5040	3.96mm (.156") Pitch KK® Solid Header, Right angle, Friction Lock, Polarised, Tin plated	10
26-60-5050	3.96mm (.156") Pitch KK® Solid Header, Right angle, Friction Lock, Polarised, Tin plated	5
26-60-5060	3.96mm (.156") Pitch KK® Solid Header, Right angle, Friction Lock, Polarised, Tin plated	5
26-60-5080	3.96mm (.156") Pitch KK® Solid Header, Right angle, Friction Lock, Polarised, Tin plated	5
26-60-5100	3.96mm (.156") Pitch KK® Solid Header, Right angle, Friction Lock, Polarised, Tin plated	5
45570-3052	MarKK™ terminal, Post-plate Tin over Nickel, 18-20AWG, loose piece	25
11-03-0016	Extraction tool	1
		226