

Square Recess Bits

1/4" Hex Insert Bits

| Part Number | Point Size | Nominal Size In. | Overall Length In. | mm |
|-------------|------------|------------------|--------------------|----|
| 950-0X | 0 | 1/16 | 1 | 25 |
| 950-1X | 1 | 3/32 | 1 | 25 |
| 950-2X | 2 | 1/8 | 1 | 25 |
| 950-3X | 3 | 9/64 | 1 | 25 |

1/4" Hex Power Drive

| Part Number | Point Size | Nominal Size In. | Overall Length In. | mm |
|-------------|------------|------------------|--------------------|-----|
| 954-0X | 0 | 1/16 | 1 15/16 | 49 |
| 954-A-0X | 0 | 1/16 | 2 3/4 | 70 |
| 954-C-0X | 0 | 1/16 | 6 | 152 |
| 954-1X | 1 | 3/32 | 1 15/16 | 49 |
| 954-A-1X | 1 | 3/32 | 2 3/4 | 70 |
| 954-B-1X | 1 | 3/32 | 3 1/2 | 89 |
| 954-C-1X | 1 | 3/32 | 6 | 152 |
| 954-2X | 2 | 1/8 | 1 15/16 | 49 |
| 954-A-2X | 2 | 1/8 | 2 3/4 | 70 |
| 954-B-2X | 2 | 1/8 | 3 1/2 | 89 |
| 954-C-2X | 2 | 1/8 | 6 | 152 |
| 954-3X | 3 | 9/64 | 1 15/16 | 49 |
| 954-A-3X | 3 | 9/64 | 2 3/4 | 70 |
| 954-B-3X | 3 | 9/64 | 3 1/2 | 89 |
| 954-C-3X | 3 | 9/64 | 6 | 152 |

1/4" Hex Power Drive – Turned Body

| Part Number | Point Size | Nominal Size In. | Overall Length In. | mm | Turned Length In. | mm |
|-------------|------------|------------------|--------------------|-----|-------------------|-----|
| 1950-0X | 0 | 1/16 | 1 15/16 | 49 | 1 1/4 | 32 |
| 1951-0X | 0 | 1/16 | 2 3/4 | 70 | 2 | 51 |
| 1950-1X | 1 | 3/32 | 1 15/16 | 49 | 1 1/4 | 32 |
| 1951-1X | 1 | 3/32 | 2 3/4 | 70 | 2 | 51 |
| 1953-1X | 1 | 3/32 | 3 1/2 | 89 | 2 3/4 | 70 |
| 1950-2X | 2 | 1/8 | 1 15/16 | 49 | 1 1/4 | 32 |
| 1951-2X | 2 | 1/8 | 2 3/4 | 70 | 2 | 51 |
| 1953-2X | 2 | 1/8 | 3 1/2 | 89 | 2 3/4 | 70 |
| 1956-2X | 2 | 1/8 | 6 | 152 | 5 1/8 | 130 |
| 1950-3X | 3 | 9/64 | 1 15/16 | 49 | 1 1/4 | 32 |
| 1951-3X | 3 | 9/64 | 2 3/4 | 70 | 2 | 51 |
| 1953-3X | 3 | 9/64 | 3 1/2 | 89 | 2 3/4 | 70 |

| | | | | |
|-------------------|-------|---------|----------|-----------|
| Screw Size | 3 & 4 | 5, 6, 7 | 8, 9, 10 | 12-14 1/4 |
| Square Point Size | 0 | 1 | 2 | 3 |

For Quad-rex bits refer to page 14.

Male Square Inserts for Pipe Plugs

1/4" to 1/2" Male Square

| Part Number | Male Hex In. | Male Square In. | Overall Length In. | mm |
|-------------|--------------|-----------------|--------------------|----|
| P-1408 | 7/16 | 1/4 | 1 1/4 | 32 |
| P-1409 | 7/16 | 9/32 | 1 1/4 | 32 |
| P-1410 | 7/16 | 5/16 | 1 1/4 | 32 |
| P-1412 | 7/16 | 3/8 | 1 1/4 | 32 |
| P-1414 | 7/16 | 7/16 | 1 1/4 | 32 |
| P-1416 | 7/16 | 1/2 | 1 1/4 | 32 |
| P-2010 | 5/8 | 5/16 | 1 1/2 | 38 |
| P-2012 | 5/8 | 3/8 | 1 1/2 | 38 |
| P-2014 | 5/8 | 7/16 | 1 1/2 | 38 |
| P-2016 | 5/8 | 1/2 | 1 1/2 | 38 |

Note: For pipe plug inserts use SC and RP bit holders found on page 26.

Double Square Recess Bits

1/4" Hex Power Drive

| Part Number | Point Size | Overall Length In. | mm |
|-------------|------------|--------------------|----|
| 954-2-DX | 2 | 1 15/16 | 49 |

1/4" Hex Power Drive – Turned Body

| Part Number | Point Size | Overall Length In. | mm | Turned Length In. | mm |
|-------------|------------|--------------------|----|-------------------|----|
| 1953-2-D | 2 | 3 1/2 | 89 | 2 3/4 | 70 |