



LAB PAL™ LABEL PRINTER

The LAB PAL™ is designed especially for laboratory applications. It offers you an easy-to-use printing system that's more effective than a pen and will enable quick and efficient sample identification.

The LAB PAL™ fits comfortably in your hand and features pre-programmed vial and slide sizes, time/date stamp and laboratory symbols, serialisation options and banner mode for general labelling. It has a built-in industrial cutter and automatic shut-off features. Operates on 6 x AA batteries or optional adaptor.



Printer Specifications

For a comparison of specifications versus other printers, see pages 248-249.

Recommended label production per day	50
Print speed	12.5mm per second
Max. Label width	19.05mm
Continuous Labels	Yes
Die cut labels	No
Print colour	Single colour printing
Memory	Last label
PC Connectivity	No
Stand-alone design	Yes
Print resolution	180dpi
Serialisation function	Yes
Barcode function	Yes - 39 and 128
Power Supply	6 x AA Batteries or AC Power Supply – both sold separately to printer

Brady's laboratory labels are designed to withstand extreme laboratory environments



DO-IT-YOURSELF LABELLING

Application Key

- F** Freezer (-70°C)
- N** Liquid Nitrogen (-196°C)
- A** Autoclave
- H** Hot Water Baths (100°C)
- L** Low-Profile (extremely thin)
- V** Vial Identification
- S** Slide Identification
- P** Plate Identification
- G** General Identification

Part No.	Reference	Description
81029	LABPAL	LABPAL Printer with full label cartridge (PAL-375-461)
81026	PAL-ACAPAC	PAL AC Adaptor
81003	PAL-IG	PAL Impact Guards
81004	LABPAL-HC	LABPAL Hardside Carrying Case

Application	Material/Colour	Part No.	Reference (9.5mm)	Part No.	Reference (12.7mm)	Part No.	Reference (19.1mm)	Roll Length (m)
F N A H L V P G	Polyester B-461 / White*	81030	PAL-375-461	81032	PAL-500-461	250085	PAL-750-461	6.4 m
F N A V P G	Nylon Cloth B-499 / White	81013	PAL-375-499	81017	PAL-500-499	81021	PAL-750-499	5.8 m
F A S P G	Polyester B-488 / White	81031	PAL-375-488	81033	PAL-500-488	250086	PAL-750-488	6.4 m
F A P G	Polyester B-423 / White	81010	PAL-375-423	81014	PAL-500-423	81018	PAL-750-423	6.4 m
F A P G	Polyester B-430 / Clear	81011	PAL-375-430	81015	PAL-500-430	81019	PAL-750-430	6.4 m
F P G	Vinyl B-439 / White**	81012	PAL-375-439	81016	PAL-500-439	81020	PAL-750-439	6.4 m

* B-461 is acceptable for use in liquid nitrogen only when wrapped upon itself, as in self-lamination

** B-439 is available in blue, green, orange, red and yellow (see ID PAL)

Plus... each cartridge comes preloaded with its own application-specific ribbon