

Electrical Markets Division
3M™ Portable Labeler PL300



Powerhouse of Portable Labelers

manufactured by:

DYMO

- Exclusive one-touch hot keys and PC connectivity for quick label formatting
- 1MB of memory to store over 1,000 labels
- Over 250 industry symbols and ability to upload graphics and logos
- Interchangeable label cartridges are easy to load, print and peel

3M

3M™ Portable Labeler PL300

The new 3M™ Portable Labeler PL300 is a revolutionary printer with unparalleled ease-of-use, unique functionality, and advanced PC connectivity. The 3M PL300 printer features exclusive one-touch “hot keys” for quick and easy creation of commonly used label types. Utilizing the 3M Portable Labeler Software, the installer can create labels before reaching the worksite or create and edit labels on site.



PC Connectivity using 3M™ Portable Labeler Software

- Upload/download label files for in-the-field and on-demand printing.
- Insert customized graphics, logos, symbols and industry terms.
- Import data from any Windows® based program.
- Create labels using the integrated step-by-step wizard.
- Print labels directly from 3M Portable Labeler Software.

Time Saving Hot Keys





Labels that stick and stay stuck.

- Won't smear, smudge or fade
- Easy to load, print and peel
- Less waste between print jobs for more return
- Engineered to stick on challenging surfaces
- Heat shrink labels

High-Performance Label Options for the 3M™ Portable Labeler PL300

		Vinyl	Nylon	Polyester	Heat Shrink	Non-Adhesive
Labels	Length	18.0'	11.5'	18.0'	5.0'	18.0'
	Width	3/8", 1/2", 3/4"	1/2", 3/4", 1"	3/8", 1/2", 3/4", 1"	1/4", 3/8", 1/2", 3/4"	1/4", 3/8", 1/2", 3/4"
	Color					
	Outdoor	X				
Surfaces	Flat	X	X	X		X
	Wiring	X	X		X	
	Flag	X	X			
	Textured	X	X	X		
Resistance	UV	X		X	X	
	Water	X		X	X	
	Chemicals	X		X	X	
	Oils	X		X	X	

3M™ Portable Labeler PL300K Specifications

3M PL300K HARD CASE KIT	
Power	Quick-charge lithium-ion rechargeable battery and on-screen battery life indicator
Warranty	1 year limited
Unit weight	5.4 lbs. (2,45 kg)
Dimensions (HxWxL)	18.6" x 4.1" x 14.4" 47,2 cm x 10,4 cm x 36,6 cm

Ordering Information

3M PL300K HARD CASE KIT	
Part No.	PL300K
UPC	0051128-58455
Includes	<ul style="list-style-type: none">· 3M Portable Labeler PL300· 3M Portable Labeler software· Durable hard carry case· 1 refill cartridge 3/4" (19 mm) black on white vinyl· 1 refill cartridge 1/2" (12 mm) black on white polyester· 3M™ Rechargeable lithium-ion Battery Pack PL300-BATPACK· 3M™ AC Adaptor and USB Cable PL-ACPS· 1 USB Cord· 1 Quick Reference Guide· 1 User Guide



DYMO is a trademark of Newell Rubbermaid. 3M is a trademark of 3M Company.

Important Notice

Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacturer for a period of twelve (12) months from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.



Electrical Markets Division
6801 River Place Blvd.
Austin, TX 78726-9000
800 245 3573
FAX 800 245 0329
www.3M.com/electrical

© 3M 2010. All rights reserved.
80-6016-0425-1 (0507.5) GP-2