

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [43030-0010](#)
Status: **Active**
Overview: Micro-Fit 3.0™ Connectors
Description: Micro-Fit 3.0™ Crimp Terminal, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 26-30 AWG, Bag

Documents:

| | |
|--|--|
| 3D Model | RoHS Certificate of Compliance (PDF) |
| Drawing (PDF) | Product Literature (PDF) |
| Product Specification PS-43045 (PDF) | |

General

| | |
|-----------------------------|----------------------------------|
| Product Family | Crimp Terminals |
| Series | 43030 |
| Application | Power |
| Crimp Quality Equipment | Yes |
| MolexKits | Yes |
| Overview | <u>Micro-Fit 3.0™ Connectors</u> |
| Product Literature Order No | 987650-5984 |
| Product Name | Micro-Fit 3.0™ |

Physical


| | |
|--------------------------------|----------------------|
| Gender | Female |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Packaging Type | Bag |
| Plating min - Mating | 1.016µm |
| Plating min - Termination | 1.016µm |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 1.27mm max. |
| Wire Size AWG | 26, 28, 30 |
| Wire Size mm² | N/A |

Material Info

UPC 800754369329

Reference - Drawing Numbers

Product Specification PS-43045, RPS-43045-003, RPS-43045-004
 Sales Drawing SD-43030-****



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[43030Series](#)

Mates With

[43031](#)

Use With

[43025](#) Receptacle Housing, [43645](#) Receptacle Housing, [44133](#) Panel Mount Receptacle Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

| Description | Product # |
|-----------------------------------|----------------------------|
| Hand Crimp Tool | 0638190000 |
| Insertion Tool for Crimp Terminal | 0638120800 |
| Extraction Tool | 0011030043 |

This document was generated on 06/14/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION