

Receptacle & Tab (Continued)

Part Numbers

Contact Design	Wire Size Range (mm ² /FLR)	Contact Finish	Micro Quadlok System		0,63 x 0,63 mm Pin Contact		Application Tooling	Hand Tool
			Strip Form	Loose-Piece	Strip Form	Loose-Piece		
Standard	0,2-0,5	tin plated	963939-1	963726-1	1-963918-1	1-963725-1	2-879130-2	73-237-2
		Au	963939-5	963726-5	1-963918-2	1-963725-2		
	0,75	tin plated	963715-1	963729-1	963716-1	963730-1	2-879501-2	73-464-1
		Au	963715-5	963729-5	963716-2	963730-2		
Single Wire Sealing System	0,2-0,5	tin plated	963725-1	963727-1	963730-1	963733-1	2-876553-2	73-416-1
		Au	963725-5	963727-5	963730-2	963733-2		
Sealing System	0,75	tin plated	963906-1	963907-1	963908-1	963909-1	2-876799-2	73-653-1
		Au	963906-5	963907-5	963908-2	963909-2		

Single Wire Seals and Dead End Plugs

Cavity Diameter	Wire Size Range (mm ² /FLR)	Single Wire Seal (mm ² /FLR)	Dead End Plug
2,54	0,20-0,35	967037-2	967036-1
	0,50-0,75	967037-1	967036-1

Special Designs

Description	Wire Size Range (mm ² /FLR)	Contact Finish	Strip Form
Receptacle Contact (Insulation Displacement)	0,35	tin plated	963997-1
Pin Contact (non-dabab)	0,2-0,5	tin plated	968918-1
	0,75	tin plated	1-963716-1

Detailed product information is available at the following Tyco Electronics companies:

Germany
Bensheim
Tel: +49-6251-133-0
Fax: +49-6251-133-600

Austria
Vienna
Tel: +43-1-277-97-0
Fax: +43-1-277-97-300

England
Stanmore Middlesex
Tel: +44-181-954-2356
Fax: +44-181-954-6234

Italy
Collegno (Torino)
Tel: +39-011-4012-111
Fax: +39-011-403-11-16

Spain
Barcelona
Tel: +34-93-291-0330
Fax: +34-93-201-7879

The Netherlands
AG 's-Hertogenbosch
Tel: +31-73-6246-246
Fax: +31-73-6246-935

Product Information Center (PIC)
Tel: +49-6251-133-999
Fax: +49-6251-133-988

Belgium
Kessel-Lo
Tel: +32-16-352-300
Fax: +32-16-352-352

France
Cergy-Pontoise Cedex
Tel: +33-1-3420-8888
Fax: +33-1-3420-8600

Poland
Warszawa
Tel: +46-22-54-90-858
Fax: +46-22-54-90-880

Sweden
Upplands Väsby
Tel: +46-8-50-72-50-00
Fax: +46-8-50-72-50-01

Czech Republic
Kurin
Tel: +420-5-41-162-111
Fax: +420-5-41-162-223

Hungary
Budapest
Tel: +36-1-280-1000
Fax: +36-1-289-1010

Portugal
Lisbon
Tel: +351-21-384-58-90
Fax: +351-21-387-71-72

Switzerland
Steinach
Tel: +41-71-447-0447
Fax: +41-71-447-0444

Tyco Electronics AMP GmbH certified according ISO 9001, QS 9000/VDA 6.1
ISO 14000 certification is in preparation

Copyright 2000 - Tyco Electronics AMP GmbH - All international rights reserved. 889761-5M-ST-11-00
Tyco Electronics AMP and ACTION PIN are registered trademarks

tyco / Electronics

AMP