


1-1838231-0 Product Details

1-1838231-0

TE Internal Number: 1-1838231-0

 [Active](#)

Miscellaneous Terminals

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Terminal Style = Bullet Terminal - Male
- Insulation Support
- Wire Range = 0.30-1.40² [22-16] mm [AWG]
- Not For Use With Double Wire
- Color = Red

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

 [Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [EURO-CRIMP INSULATED RED MALE BULLET TERMINAL 0.5mms...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- [Euro-Crimp Terminals and Splices](#) (PDF, English)

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Insulation Support](#) = Insulation Support
- Color = Red
- Material = Brass
- Finish = None
- Insulation Diameter (mm [in]) = 3.56 [.140] Max.
- Insulation Material = PVC
- Proprietary Name = EURO-CRIMP

Body Related Features:

- Terminal Style = Bullet Terminal - Male
- [Wire Range \(mm \[AWG\]\)](#) = 0.30-1.40² [22-16]
- Double Wire = No

Housing Related Features:

- Bullet Diameter (mm [in]) = 4.00 [0.157]

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- Packaging Method = Loose Piece

Other:

- Brand = AMP

 [BOOKMARK](#)


Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)