

**BMP®21 Mobile Printer, ID PAL™ & LABPAL™
Label Printer Labels - # M21-750-499**



SIZE:	0.750" W x 16' H (19.050 mm W x 4.880 m H)
MATERIAL:	Nylon Cloth
QTY/UOM:	1/Roll
CATALOG #:	M21-750-499
PRODUCT #:	110895

OVERVIEW **SPECIFICATIONS**

Description for BMP®21 Mobile Printer, ID PAL™ & LABPAL™ Label Printer Labels

Nylon cloth labels for the BMP®21 Mobile Printer, ID PAL™ and LABPAL™ Label Printers. Black ribbon on white tape.

Specification Of BMP®21 Mobile Printer, ID PAL™ & LABPAL™ Label Printer Labels

Application(s):	Communications Cables, General Identification, Laboratory Identification, Panel Identification, Plate, Vial, Voice/Data Identification, Wire & Cable Marking
Agency Approval (s)/Compliance:	Halogen-Free (DIN VDE 0472/parts 815), UL Recognized
Size:	0.750" W x 16' H (19.050 mm W x 4.880 m H)
Printable Area:	0.750" W x 16' H (19.050 mm W x 4.880 m H)
Label Type/Style:	Label
Color:	Black on White
Finish:	Matte
Qty Per Row:	1
Material Type:	Nylon Cloth
Material Description:	Nylon Cloth
Brady Material #:	B-499
Safety Catalog:	pg. 116
General ID Catalog:	pg. 15
Cable Type:	100 Pair Copper, 2 Pair Fiber, 25 Pair Copper, 4 Pair STP, 4 Pair UTP, 4-12 Pair Fiber, 50 Pair Copper, Backbone Cable, Cable Bundles, CAT 5, CAT 5E, CAT 6, Fiber Strand, Fiber/Coax, RG-59 Coax, RG-6 Coax, Silver Satin
Environment:	Autoclave, Freezer, Liquid Nitrogen
Printer Compatibility:	BMP21, ID PAL, LABPAL
Surface:	Highly Textured, Low Surface Energy, Powder Coated, Smooth, Textured/Rough
Special Properties:	High adhesion, Low profile
RoHS Compatibility:	Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.
QTY/UOM:	1/Roll