

1 Port PCI 10/100/1000 32 Bit Gigabit Ethernet Network Adapter Card

StarTech ID: ST1000BT32



This PCI-based 10/100/1000 Mbps Gigabit Ethernet Network Adapter Card provides a simple connection to a Gigabit Ethernet network, and is fully compatible with IEEE 802.3, 802.3u, 802.3ab and 802.3x standards.

Suitable for any PCI-enabled client, server or workstation, the Gigabit Ethernet Network Adapter Card supports high performance dual channel networking and maximum data transfer speeds of 1000Mbps in each direction (2000 Mbps total) - up to ten times faster than 10/100 Ethernet.

Compatible with a broad range of operating systems, including Linux, Windows 98SE, ME, 2000, XP, XP-64bit, Vista, Vista-64bit, 7, 7-64bit as well as Mac OS 10+, this high quality PCI Gigabit NIC includes an optional low profile bracket that makes it easy to install the card in a small form factor/low profile computer case/server.

Applications

- Add an additional Ethernet port to a workstation or server computer for redundancy
- Upgrade a computers 10/100 Ethernet port to a 1000 compatible port
- Add networking capabilities to an old system with no Ethernet port

Features

- A single 10/100/1000Mbps compatible RJ45 Ethernet port
- Network Link/Activity and 10/100/1000 Mbps LED indicators
- Fully Compliant with IEEE 802.3, IEEE 802.3u, IEEE 802.3x, and IEEE 802.3ab, and supports IEEE 802.1Q VLAN tagging
- Full and half duplex support
- Supports Wake-on-LAN function
- Crossover Detection & Auto-Correction (Auto MDI/MDI-X)
- Includes a low profile installation bracket

Technical Specifications

Warranty	Lifetime
Ports	1
Bus Type	PCI / PCI-X (5 / 3.3V)
Card Type	Standard Profile (LP bracket incl.)
Industry Standards	IEEE 802.3, IEEE 802.3ab, IEEE 802.11u PCI 2.1, 2.2
Chipset ID	Realtek - RTL8110SC
Connector Type(s)	1 - PCI / PCI-X (Universal 3.3 & 5V; 32-bit) Male
External Ports	1 - RJ-45 Female
MTBF	36,000 Hours
Maximum Data Transfer Rate	1000 Mbps
Compatible Networks	10/100/1000 Mbps
Full Duplex Support	Yes
Supported Protocols	CSMA/CD
OS Compatibility	Windows 98SE/ ME/ NT/ 2000/ XP(32/64-bit)/ Server 2003(32/64-bit)/ Server 2008 R2/ Vista(32/64-bit)/ 7(32/64-bit)/ 8(32/64-bit) Netware Server 5.x, Netware ODI for DOS Linux and Unix
Product Length	123 mm [4.8 in]
Product Width	20 mm [0.8 in]
Product Height	63 mm [2.5 in]
Product Weight	54 g [1.9 oz]
LED Indicators	1 - 10/100/1000 Mbits/sec Link/Activity
Operating Temperature	0°C to 55°C (32°F to 131°F)
Humidity	10% ~ 95% RH
Note	IRQ Line & I/O Address allocated by system
Package Quantity	1
Shipping (Package) Weight	0.1 kg [0.3 lb]
Included in Package	1 - Gigabit Ethernet PCI Card
Included in Package	1 - Low Profile bracket
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

