

**Cutting, stripping and crimping tool  
STRIPAX PLUS 2.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Cutting, stripping and crimping tools for  
connected wire-end ferrules strips**

- Cutting
- Stripping
- Crimping
- Automatic feeding of wire end ferrules
- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- Efficient: only one tool needed for cable work, and thus significant time saved

**General ordering data**

Order No.	<a href="#">9020000000</a>
Type	STRIPAX PLUS 2.5
Version	Cutting, stripping and crimping tool, Crimping tool for wire-end ferrules, 0.5 mm <sup>2</sup> , 2.5 mm <sup>2</sup> , Trapezoidal crimp
GTIN (EAN)	4008190067267
Qty.	1 pc(s).

**Cutting, stripping and crimping tool  
STRIPAX PLUS 2.5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Length	210 mm	Weight	260 g
Net weight	250.91 g		

**Technical data**

Version	Mechanical, without interchangeable inserts
---------	---

**Contact description**

Type of contact	Strips of linked wire-end ferrules	Crimping range, min.	0.5 mm <sup>2</sup>
Crimping range, max.	2.5 mm <sup>2</sup>		

**Tool data - crimping**

Crimping profile 1, min.	0.5 mm <sup>2</sup>	Crimping type/profile	Trapezoidal crimp
Wire end ferrules cross-section, min.	0.5 mm <sup>2</sup>	Crimping profile 1, max.	0.75 mm <sup>2</sup>
Wire end ferrules cross-section, max.	2.5 mm <sup>2</sup>	Crimping profile 2, min.	1 mm <sup>2</sup>
Crimping profile 2, max.	1.5 mm <sup>2</sup>	Crimping profile 3, min.	2.5 mm <sup>2</sup>

**Classifications**

ETIM 2.0	EC000168	ETIM 3.0	EC000168
UNSPSC	23-17-16-04	eClass 4.1	21-04-03-01
eClass 5.1	21-04-03-01	eClass 6.0	21-04-38-90
eClass 7.0	21-04-38-90		

**Product information**

Descriptive text ordering data	Additional accessories can be found in chapter J
Descriptive text technical data	Only strip-type products from Weidmüller may be processed. The use of wire-end ferrules on reels may lead to destruction.
Description of article	Crimping tool
Product description	• For processing linked wire-end ferrules from Weidmüller 0.5...2.5 mm <sup>2</sup> (~AWG 20...14)

**Approvals**

Approvals



**Cutting, stripping and crimping tool  
STRIPAX PLUS 2.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

