


E501001 Cord Sets - DataTuff® Cat 5e IP20 RJ45 Cord Set

For more Information
please call

1-800-Belden1

General Description:

1 meter (3.3 ft.), Unshielded with solid conductors (ref: Belden Bonded-Pair Cable 7923A). Cable Rating NEC: CMR, CMX-Outdoor. CEC: CMR FT4. MSHA.

Notes (Overall)

Notes: For additional information about this product, visit our web site at <http://www.belden.com>

Cable

Description:	4 pair, 24 AWG bare copper, Polyolefin Insulation, Bonded pairs, Industrial Grade PVC, Oil Res, Sun Res, P-MSHA, CMR, CMX-Outdoor, FT4.
Part Number:	7923A
Shielding:	Unshielded
Electrical Performance:	Category 5e
Maximum Operating Voltage:	300 V RMS
Applicable Standards:	ANSI/TIA/EIA-568-C.2, ISO/IEC 11801, EtherNet/IP(tm) Specification, UL 1666 Riser

Connectors

Description:	RJ45 plugs Suitable for use in IP20 unsealed applications
Connector Type:	Cat 5e
Sealing:	Suitable for IP20
Connector Interface:	IEC 60603-7
Shielding:	Unshielded
Electrical Performance:	Cat 5e
Maximum Operating Voltage:	300 V RMS
Applicable Standards:	ANSI/TIA/EIA-568-C.2, ISO/IEC 11801, EtherNet/IP Specification

Assembly

Part Number:	E501001
Electrical Performance:	Category 5e
Maximum Operating Voltage:	300 V RMS
Storage Temperature Range:	-40°C To +70°C
Installation Temperature Range:	-10°C To +60°C
Operating Temperature Range:	-10°C To +60°C
Applicable Standards:	ANSI/TIA/EIA-568-C.2, ISO/IEC 11801
Shielding:	Unshielded
Length:	1 meter (3.3 ft.)

Notes: US Patent #'s 5, 606, 151; 5, 734, 126, EtherNet/IP is a trademark of ControlNet International, Ltd. under license by Open DeviceNet Vendor Association, Inc.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
E501001 010S1	1 EA	0.251 LB	BLACK		CORDSET IP20 CAT5E UTP SO 1M

Test Reports

a) UL

- i) UL Test Reports are available on-line through the UL Client Document Access web portal.
- ii) UL Inspection Reports are also available through the UL Client Document Access web portal.

b) CSA

- i) CSA "Descriptive Report and Test Results" documents are available on the CSA Gateway Portal.
- ii) CSA Inspection Reports are maintained on the CSA issued 'flash drive' at each manufacturing location.

* other test data may be available if requested at time of order.

Revision Number: 1 Revision Date: 01-24-2012

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.