



APPROVAL MARKING TABLE:

				NXXXXX	
			E62405	X	
				X	
		X SANS164-1			

APPROVED SOURCE FOR CABLE

1. BAO HING(SHENZHEN).

PLUG TYPE	IEC 60320-2-2, EN 60320-2-2, STANDARD SHEET E GB17465.2
CONNECTOR TYPE	C13
CABLE OUTER DIAMETER	6.0~7.6
TEMPERATURE	75°C
CORDSET RATING(AMP/VOLTAGE)	10A 250V

CUSTOMER APPROVED :

APPROVED BY :	
SIGNATURE :	
APPROVED DATE :	

ISSUE	REF. NO.	DESCRIPTION	DATE
		REMOVE KC LOGO FM. PLUG & CONNECTOR MARKING.	
002	HG11-030-12	CHANGE TITLE FM. 'UNIVERDAL' TO 'EUROPEAN+CHINESE +NORTH-AMERICAN'.	12/11/12
003	HG11-242-12	CHANGE THE FORMAT FM. '2 PCS SPEC.' TO 'ONE PAGE SPEC.'.	03/12/12

NOTE :

1. ALL DIMENSIONS IN mm.
2. THIS PART CAN BE MANUFACTURED AT ANY LOCATION WHICH HAS SAFETY APPROVAL.
3. RoHS COMPLIANT.
4. LABEL DETAILS:
REFER TO LABEL DWG. NO.: VL-0356.
5. PACKAGING QTY : 120 PCS PER CARTON.
6. THE WITHDRAWAL FORCE OF CONNECTOR V1625 IS ABLE TO MEET 30N~45N WHEN MATING WITH THE APPLIANCE INLET WITH NOMINAL DIMENSIONS.
7. CARTON BOX MUST HAVE A LABEL/STAMP SAYING : " THIS PACKAGE CONTAINS CORDS HAVING GROUNDING CONDUCTOR WITH GREEN/YELLOW COLOUR INSULATOR, GROUNDED CONDUCTOR WITH BLUE COLOUR INSULATOR AND LIVE CONDUCTOR WITH BROWN COLOUR INSULATOR ".

5	PRINTED LABEL	VL-0356	1
4	6" PE TIE BLK	6310056	1
3	IP60G NL7976B BLK	4100115	-
	MOLDED CONNECTOR V1625 (10A 250V)	V1625	1
2	IP60G NL7976B BLK	4100115	-
	MOLDED PLUG VAC14S (10A 250V)	VAC14S-BK	1
1	H05VV-F 3X0.75+SVT 18/3 75°C+		
	RW 3X0.75 BLK LF (EURO+UL/CSA+CCC)	1220031	1
S/N	DESCRIPTION	ITEM NUMBER	QTY
TITLE : EUROPEAN+CHINESE+NORTH-AMERICAN JUMPER CORDSET (PB FR)		SCALE : N.T.S.	
CUSTOMER : VNA/VOLEX INC		PAGE : 1/1	
CUSTOMER PART NUMBER : 2172H		ISSUE	
Reference Number : 113103/3 (HG11-242-12)		003	
SALES :	QA :	ENGRG :	CHECKED BY :
	DRAWN BY : YA LING	Voilex (Asia) Pte Ltd	
Date :	Date : 4/12/12	Date : 4/12/12	Date : 03/12/12
<small>Confidential property of Voilex. Information contained herein shall not be disclosed to others, reproduced or used for any other purposes except as authorized in writing by an authorized official of voilex asia.</small>			