



### HeadsUp Lite™ 2620 Flashlight

A hybrid LED/Xenon hands-free flashlight. The 2620 gives you the option of using the Xenon lamp for intense bright light or 3 LEDs to conserve battery life. The multi-angle pivoting head allows you to aim light where you need it. A rubber strap for hard hat use and adjustable cloth strap for bare head use are both included. The HeadsUp Lite 2620 is perfect for hiking, camping, or for any task that require both hands. Powered by 3 AAA alkaline cells (included)

Body Material: ABS Resin

Minimum Pack 1 ea.

Packaged Weight: 8.3 oz.

### HeadsUp Lite™ 2620 Flashlight Specifications

### HeadsUp Lite™ 2620 Flashlight Configurations

| Cat. # | Description |
|--------|-------------|
|--------|-------------|

|                             | High                      | Low       |
|-----------------------------|---------------------------|-----------|
| <b>LIGHT SOURCE</b>         | Xenon (High)              | LED (Low) |
| <b>BATTERIES</b>            | 3 AAA Alkaline (Included) |           |
| <b>CHARGE TIME</b>          | N/A                       |           |
| <b>VOLTAGE</b>              | 4.5                       |           |
| <b>LENGTH</b>               | 2.16" (5.5 cm)            |           |
| <b>WEIGHT w/ BATTERIES</b>  | 4.8 oz. (0.14 kg)         |           |
| <b>WEIGHT w/o BATTERIES</b> | 3.5 oz. (0.1 kg)          |           |

|                                      | FL1 STANDARD                                                                        | High      | Low       |
|--------------------------------------|-------------------------------------------------------------------------------------|-----------|-----------|
| <b>LIGHT OUTPUT</b>                  |    | 26 LUMENS | 14 LUMENS |
| <b>RUNTIME (hours/min)</b>           |    | 2h 15m    | 18h       |
| <b>BEAM DISTANCE (meters)</b>        |    | 44m       | 29m       |
| <b>PEAK BEAM INTENSITY (candela)</b> |    | 491cd     | 216cd     |
| <b>WATER RESISTANT</b>               |  | IPX4      | IPX4      |

## HeadsUp Lite™ 2620 Flashlight Approvals



II 3 G EEx nL IIC T3X  
Certificate: TRL Report# XU1006/4804



Class I, Div. 1, GP C,D, T3C CONFORMS TO STD. UL 783

2620 HeadsUp Lite™ 2620 Flashlight (Carded)

## NSN List

| NSN #            | Description  |
|------------------|--------------|
| 6230-01-513-8446 | 2620RS Black |

## HeadsUp Lite™ 2620 Flashlight Accessories

| Cat. # | Description                           |
|--------|---------------------------------------|
| 2624   | HeadsUp Lite™ 2620 Lamp               |
| 2625   | Red LED Flashing/Constant Alert Light |
| 2626   | Replacement Rubber Strap              |
| 2627   | Replacement Cloth Strap               |

## Pelican Products, Inc.

23215 Early Avenue • Torrance, CA 90505 • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311  
e-mail: [CSR.Consumer@pelican.com](mailto:CSR.Consumer@pelican.com) • [www.pelican.com](http://www.pelican.com)