

RoHS  
Compliant



## Features:

- This iron is a fixed temperature 15W 230V soldering iron fitted with a 1.5m lead and a standard British plug.
- A standard chrome plated soldering bit type 1,100 is fitted to the main element.

## Specifications:

Output Power	: 25W
Heat Temperature Range	: +390°C
Supply Voltage	: 230V AC
Plug Type	: UK
Breakdown Voltage	: 2,500V Max.
Colour	: Black
Body Length	: 122mm
External Diameter	: 23mm
Lead Length	: 1.5m
Length	: 200mm
Power Rating	: 25W
Tip / Nozzle Style	: Chisel
Weight	: 180g

## Fixed Temperature Soldering Irons:

### 15W and 25W:

- 230V AC operation
- Light weight ergonomic design
- Strong high quality polycarbonate handle
- Fitted with moulded UK 3-Pin mains plug
- All the replacement tips are iron and chrome plated

# Soldering Iron



Description	15W	25W
Lead	1.5m , 3 - Core 3 x 0.75mm <sup>2</sup> insulated PVC with strain relief	-
Max. Tip Temperature (°C)	370	390
Handle Length	122	
Total Length (Including Tip)	200	
Handle Diameter	23 (Bottom), 17 (Flex End)	
Breakdown Voltage (V)	2,500	
Standard Tip Fitted	2.3 (Chisel)	3 (Chisel)

Tip Size	Style
<b>Tips for use with 15W iron (370°C)</b>	
0.1	Point
1	Chisel
2.3	
3	
4.7	

Dimensions : Millimetres

Tip Size	Style
<b>Tips for use with 25W iron (390°C)</b>	
0.5	Point
2.3	Chisel
	Screwdriver
3	Chisel
	Screwdriver
4.7	Chisel

Dimensions : Millimetres

## Part Number Table

Description	Part Number
Soldering Iron, 15W, 230V, UK Plug	5061921
Soldering Iron, 25W, 230V, UK Plug	5061933

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com  
www.farnell.com  
www.newark.com

