

VS-08-RJ45-5-Q/IP67

Order No.: 1656990

<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=1656990>

RJ45 plug-in connector, IP20, CAT5e, 8-pos., with QUICKON fast connection technology, for 26 ... 24 AWG 1-wire and 7-wire conductors, for cable diameter of 5.0 mm ... 8.0 mm, labeling: TIA 568 B, color: gray


Ethernet**Product notes**

WEEE/RoHS-compliant since:
20/10/2006



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Commercial data

EAN	 4 046356 081399
Pack	1
Customs tariff	85366990
Gross weight in pieces	31.60 g
Country of Origin	DE
Catalog page information	Page 287 (PC-2011)

Technical data**Mechanical characteristics**

Number of positions	8
Connection profile	RJ45 8(8)
Shielded	Yes
Insertion/withdrawal cycles	≥ 1000

Connection method	IDC fast connection
Conductor cross section	0.13 mm ² ... 0.32 mm ² (solid) 0.14 mm ² ... 0.36 mm ² (stranded)
Connection cross section AWG	26 ... 24 (solid) 26 ... 24 (stranded)
External cable diameter	5 mm ... 8 mm
Cable exit	Straight
Color	Military gray RAL 7042
Ambient temperature (operation)	-20 °C ... 70 °C

Material data

Inflammability class according to UL 94	V0
Housing material	PA
Contact carrier material	PC
Contact material	Copper alloy
Contact surface material	Gold over nickel
Material, O-ring	FPM
Cable seal material	NBR
Material housing intermediate seal	NBR
Degree of protection	IP67

Electrical characteristics

Number of positions	8
Transmission characteristics (category)	CAT5 (IEC 11801:2002), CAT5e (TIA 568B:2001)
Rated current	1.75 A
Surge voltage category	I
Pollution degree	2

Certificates



Certification

cULus Recognized

Certifications applied for:

Certification Ex:

Accessories


Item	Designation	Description
------	-------------	-------------

Marking

0814775	VS-ZBFM-8-SET	Set of marker labels, For terminal block width: 8.2 mm
---------	---------------	--

Drawings

Dimensioned drawing



RJ45 plug connectors, IP67, QUICKON fast connection technology

Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford / Shropshire / TF7 4PG,England
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.
Technical modifications reserved;