

Data Sheet - X401U

ASUS X401 notebooks offer a colourful choice with a thin and light design

Smartphone-like responsiveness with instant on*

Only ASUS notebooks offer you true 2-second instant on resume from sleep or hibernate, cutting out long reboot times and putting you back to work or enjoyment right where you left off. Thanks to ASUS Super Hybrid Engine II technology, you also get up to 14 days of standby, with auto data backup should battery charge drop to 5% or less.

Stay comfortable with IceCool technology

Exclusive ASUS engineering has created a unique internal layout that keeps heat away from palm rests and from users. Always below body temperature, palm rests feel cool to the touch, and are therefore more comfortable to use even during long sessions.

SonicMaster Lite audio amazement

Exclusive ASUS sound enhancement turns the new X Series into highly capable multimedia notebooks, with the best sound in their class: more power, wider range, and improved clarity combine to offer a more satisfying multimedia experience.



X401U-WX031H

Processor	AMD® C60
OS	Windows 8 (64bit)
Display	14.0" LED-backlit Slim TFT LCD display (HD 1366x768/ 16:9)
Graphic Card	Integrated Intel® GMA HD
Storage	320GB (5400rpm)
Memory	4G (4096x1)
Type	DDRIII 1333 MHz
ODD	No ODD
Wireless	802.11 BGN
LAN	10/100/1000 Mbps
Security	LoJack
Webcam	0.3 Mega Pixel web camera
Battery	6 cell
Warranty	1 year global
Card Reader	2 -in-1 card reader (SD/ MMC)
Interface	1 x Line-in Jack 1 x Headphone-out & Audio-in Combo Jack 1 x RJ45 LAN Jack for LAN insert 1 x VGA Port (D-Sub) 1 x HDMI 1 x USB 3.0 1 x USB 2.0
Audio	Built-in speaker, Built-in microphone Altec Lansing® speakers
LED Status Indicator	HDD Power-on/Suspend Capital Lock Wireless on status indicator Bluetooth on status indicator
Software	ASUS Win flash, ASUS Face Logon, ASUS Life Frame III, Virtual Camera, ASUS Live Update, Power4Gear Hybrid, Fast Boot, GamePark Console (JPN image not installed), ASUS APBANK (JPN image not installed), ASUS WebStorage, ASUS Wireless Console 3, Windows Live4 package & Toolbar, eManual, E-Driver, ASUS Vibe, ASUS AiRecovery, ASUS Color Enhancement (ASUS Splendid), ASUS SceneSwitch, ASUS DVD player v9, Instant on, USB Charger+
Dimension & weight	34.1 x 23.5 x 2.65 ~ 3.23cm (WxDxH) 1.85 kg (with 6 cell battery) Product Box: 40.5 x 29.4 x 8.5 cm (WxDxH) Box with Contents weighs 3.50kg
Order Code	90N4OA125E0214VL138
Colour	Black (Matte)

*Actual X401 standby time may vary due to specific component performance, connected devices, and environmental differentiation.