

STEALTH 7000™

CLEAR FRAME - HC LENS (K)

TECHNICAL SPECIFICATION

PRODUCT CODE: ASA430-021-300

CONTOUR DESIGN & FLEXIBILITY OF FRAME GIVES A GOOD VERSATILE FIT ONTO BOTH SMALLER & LARGER FACES

EYE & FACE PROTECTION

INSTRUCTIONS FOR USE

In use ensure that the safety spectacles fit comfortably and securely on the head

Ensure that the safety spectacles are in place, before entering the hazard area

FRAME:
Polycarbonate




LENS:
Polycarbonate

STEALTH 7000

PERFORMANCE

Lens and frame offer protection against low energy high-speed particles at 45m/s (101mph)

The optical qualities of the lens comply with the requirements of optical class 1 (highest)



CONFORMITY

Conforms to EN 166 1.F.T (K or N) & EN 170

EC Certificate Number 726, issued by Inspec Certification Limited



CLEANING & MAINTENANCE

The safety spectacles may be cleaned with soap and warm water and dried with a soft cloth

Do not clean with chemical or abrasive cleaners

The eye shield should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature



MANUFACTURING FOR SAFETY
WWW.JSP.CO.UK

UKSALES@JSP.CO.UK
TEL: +44 (0)1993 826050



STEALTH 7000™

CLEAR FRAME - HC LENS (K)

TECHNICAL
SPECIFICATION

PRODUCT CODE: ASA430-021-300


CONTOUR DESIGN & FLEXIBILITY OF FRAME GIVES A GOOD VERSATILE FIT ONTO BOTH SMALLER & LARGER FACES

EYE & FACE PROTECTION

DIMENSIONS OF OUTER PACKAGING

Quantity: 10

Weight: 0.5kg (Approx.)



WIDTH:
172mm

LENGTH:
290mm

HEIGHT:
85mm




STEALTH 7000

DIMENSIONS OF OUTER PACKAGING

Quantity: 120

Weight: 3.7kg (Approx.)



WIDTH:
315mm

LENGTH:
545mm

HEIGHT:
377mm

DIMENSIONS OF SPECTACLE

Lens Thickness: 3mm

Lens Size (Vertical): 43mm

Lens Size (Diagonal): 81mm

Bridge: 12mm

Temple Length (Lens to tip): 162mm

Overall Width: 145mm

Closest point between temple tips: 86mm

Weight: 24g (Approx.)

MARKINGS

Frame: EN166 1.FT

Clear Lens:	2-1.2	↑	1.FT (K or N)
Amber Lens:	2-1.2	↑	1.FT.K
Orange Lens:	2-1.7	↑	1.FT.K
Smoke Lens:	5-2.5	↑	1.FT.K
Green Lens:	2-3	↑	1.FT.K

LIMITATIONS OF USE

Protection will only be offered if the safety spectacles are fitted correctly

If the safety spectacles become scratched or damaged they should be replaced, likewise if the safety spectacles are subjected to severe impact they should be replaced immediately

Do not apply paint, solvents, adhesives or self-adhesive labels, except in accordance with instructions from the manufacturer

The safety spectacles, when in contact with the skin may cause allergic reactions to susceptible individuals. If this occurs leave the hazard area, remove the eye shield and seek medical advice

The attention of users is also drawn to the dangers of modifying or removing any of the original component parts, other than as recommended by the manufacturer

The Stealth 7000™ is not suitable for protection against dusts, liquids or molten metals