

## **2 Port USB Keyboard Mouse Switch Cable w/ File Transfer for PC and Mac®**

*StarTech ID: SVKMS2*



The SVKMS2 2 Port USB Keyboard Mouse Switch Cable w/ File Transfer for PC and Mac® enables you to control two computer systems using a single keyboard and mouse set, and offers the ability to transfer files between the connected Windows® and/or Mac systems.

Offering automated installation (no additional software or drivers required), this compact KM switch cable connects your Windows and/or Mac systems using a standard USB 2.0 port to make switching between systems as simple as moving the mouse over to your second display, or using hot-keys.

This simple 2 port USB KM switch also provides the added benefit of clipboard sharing so you can copy and paste text from one system to another, or drag and drop files for effortless transfers and data management.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### **Applications**

- Perfect for office applications where multiple computers need to be controlled by a single user and desk space is limited
- Great for PC repair or tech bench environments, allowing you to control and monitor two systems simultaneously
- A convenient solution for the business user needing to transfer files between their desktop and laptop systems

### **Features**

- Keyboard and mouse sharing between 2 computers
- Compatible with Windows® and Mac® systems
- Simple switching between systems via mouse movement, or hot-keys
- Drag and drop file transfer
- Copy and paste text between systems
- Plug-and-Play, no software/driver CD required

## Technical Specifications

Warranty	2 Years
KVM Ports	2
PC Interface	USB
Rack-Mountable	No
Cables Included	Yes
Chipset ID	MCT - WH88
Daisy-Chain	No
Host Connectors	2 - USB A (4 pin) Male
IP Control	No
Maximum Number of Users	1
OS Compatibility	Windows® 8 (32/64bit), 7 (32/64), Vista(32/64), XP(32/64), 2000 Mac OS 10.6 - 10.8
Microsoft WHQL Certified	Yes
Cable Length	1.8 m [6 ft]
Color	Black
Enclosure Type	Plastic
Product Length	1.8 m [6 ft]
Product Width	18.5 mm [0.7 in]
Product Height	11.5 mm [0.5 in]
Product Weight	42 g [1.5 oz]
LED Indicators	2 - Power / Link
Power Adapter Included	USB-Powered
Operating Temperature	0°C to 50°C (32°F to 122°F)
Storage Temperature	-10°C to 55°C (14°F to 131°F)
Humidity	85% RH (Non-Condensing)
Shipping (Package) Weight	121 g [4.3 oz]
Included in Package	1 - Keyboard Mouse Sharing Cable
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

