

## Portable 4 Port SuperSpeed Mini USB 3.0 Hub - Black

StarTech ID: ST4300MINU3B



The ST4300MINU3B Portable 4 Port SuperSpeed Mini USB 3.0 Hub (Black) lets you expand your USB connectivity by turning a single USB 3.0 port into four external USB 3.0 ports. The integrated cable design makes this mini USB hub the perfect accessory for your Mac® / PC notebook or Ultrabook™ computer.

The 4 Port USB 3.0 hub supports USB 3.0 data bandwidth (5 Gbps - up to 10x more than USB 2.0) and is backward compatible with USB 2.0 and 1.1 devices, ensuring flawless performance from all of your USB peripherals/devices, regardless of their age.

Ideal for home and business users who require portability, the external USB 3.0 hub is USB-powered and features a rugged, compact design with a built-in cable so no additional cables are needed to connect the hub to your system.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Applications

- Notebook / Ultrabook™ users with limited USB 3.0 ports and multiple USB 3.0 devices
- Make hard to access USB ports more accessible, by being able to position the hub anywhere the cable will reach
- Separate tightly packed USB ports, to better accommodate larger USB plugs or prevent overcrowding

### Features

- Four USB type-A ports that can be accessed simultaneously
- SuperSpeed USB 3.0 compliant, with data transfer rates up to 5 Gbps
- Backward compatible with USB 2.0 and USB 1.0/1.1 specifications and devices
- Compact and portable design with built-in cable
- Plug-and-Play and hot-swap compatible

Technical Specifications

Warranty	2 Years
Bus Type	USB 3.0
Chipset ID	Genesys - GL3522
Interface	USB 3.0
Ports	4
External Ports	1 - USB 3.0 A (9 pin; SuperSpeed) Male
External Ports	4 - USB 3.0 A (9 pin; SuperSpeed) Female
Maximum Data Transfer Rate	5 Gbps
Type and Rate	USB 3.0 - 5 Gbit/s
OS Compatibility	Windows® 8(32/64bit), 7(32/64), Vista(32/64), XP(32/64) Mac OS 10.0 – 10.8
Cable Length	145 mm [5.7 in]
Color	Black
Enclosure Type	Plastic
Product Height	14 mm [0.6 in]
Product Length	80 mm [3.1 in]
Product Weight	38 g [1.3 oz]
Product Width	36 mm [1.4 in]
LED Indicators	1 - Power
Power Adapter Included	USB-Powered
Humidity	0~80% RH
Operating Temperature	0°C to 40°C (32°F to 104°F)
Storage Temperature	-20°C to 60°C (-4°F to 140°F)
System and Cable Requirements	Available USB Port
Shipping (Package) Weight	112 g [4 oz]
Included in Package	1 - 4 Port USB 3.0 Hub
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

