

# SpikesShield® Power Quality Products Surge Protection Plug Strips

15 Ampere, 125 Volts 50/60Hz



## SpikesShield® Surge Protective Devices

### Plug-in Style Surge Outlets

Description	# of Outlets	Joule Rating	Peak AMP Rating	Cord Length	Color	Warranty	Catalog Number
Single outlet plug-in SPD	1	750	13.5kA	N/A	Off. White	N/A	<b>HBL1PI750</b>
Single outlet plug-in SPD w/phone line protection	1	750	13.5kA	N/A	Off. White	N/A	<b>HBL1PI750M</b>
Single outlet plug-in SPD w/CATV protection	1	750	13.5kA	N/A	Off. White	N/A	<b>HBL1PI750C</b>
Three outlet plug-in SPD	3	750	13.5kA	N/A	Off. White	N/A	<b>HBL3PI750</b>



**HBL1PI750 HBL1PI750M**



**HBL1PI750C HBL3PI750**

## SpikesShield® Surge Protection Plug Strips

### Metallic Strips

Description	# of Outlets	Joule Rating	Peak AMP Rating	Cord Length	Color	Down Line Warranty	Catalog Number
Metal Power Strip (No surge protection)	6	N/A	N/A	6'	Off. White	N/A	<b>HBL6MPS</b>
Metal SPD	6	1050	19.5 kA	6'	Off. White	\$2,500	<b>HBL6MPS1050</b>
SPD w/Wire Management	6	350	6.5 kA	6'	Yellow	\$2,500	<b>HBL6PS350YL</b>
SPD w/Wire Management	8	350	6.5 kA	6'	Yellow	\$2,500	<b>HBL8PS350YL</b>
Heavy Duty SPD w/HBL5252BK Receptacles	6	450	30 kA	6'	Black	N/A	<b>HBL6PS</b>
Heavy Duty SPD w/HBL8200HW Receptacles	6	450	30 kA	6'	Black	N/A	<b>HBL6PSHG</b>



**HBL6MPS**



**HBL6PS**

### Non-Metallic Strips \*

Description	# of Outlets	Joule Rating	Peak AMP Rating	Cord Length	Color	Down Line Warranty	Catalog Number
Power Strip (No surge protection)	6	N/A	N/A	6'	Off. White	N/A	<b>HBL6PPS</b>
SPD	6	350	6.5 kA	6'	Off. White	\$2,500	<b>HBL6PS350A</b>
SPD	6	350	6.5 kA	15'	Off. White	\$2,500	<b>HBL6PS35015A</b>
SPD	6	350	6.5 kA	25'	Off. White	\$2,500	<b>HBL6PS35025A</b>
SPD w/Fax/Modem	6	1050	19.5 kA	6'	Off. White	\$2,500	<b>HBL6PS1050MA</b>
SPD	7	1050	19.5 kA	6'	Off. White	\$10,000	<b>HBL7PS1050A</b>
SPD w/Fax/Modem	7	1050	19.5 kA	6'	Off. White	\$10,000	<b>HBL7PS1050MA</b>
SPD	7	1050	19.5 kA	15'	Off. White	\$10,000	<b>HBL7PS105015A</b>
SPD w/Fax/Modem/CATV	8	2100	39 kA	6'	Off. White	\$25,000	<b>HBL8PS2100MA</b>
SPD w/Fax/Modem/CATV/DSS	8	2100	39 kA	6'	Off. White	\$25,000	<b>HBL8PS2100DA</b>



**HBL6PS350YL**



**HBL6PS350A**

### Specialty Non-Metallic Surge Strips

Description	# of Outlets	Joule Rating	Peak AMP Rating	Cord Length	Color	Down Line Warranty	Catalog Number
SPD w/Two USB Ports	4	1050	19.5 kA	6'	Black	\$10,000	<b>HBL4PS1050USB</b>
Remote Switch SPD w/One Keychain Ring Control	6	2100	39 kA	6'	Off. White	\$25,000	<b>HBL6RSPS2100</b>
Energy Saving SPD w/Master/Slave Design w/Fax/Modem	8	1050	19.5 kA	6'	Off. White	\$10,000	<b>HBL8ESPS1050M</b>
Energy Saving SPD Master/Slave Design w/CATV Protection	8	1050	19.5 kA	6'	Off. White	\$10,000	<b>HBL8ESPS1050C</b>



**HBL8PS2100MA**

Note: \* See Section X, page X-10 for TR description.



**HBL8PS350YL**



**HBL6RSPS2100**



**HBL8ESPS1050M**