



# T&B<sup>®</sup>

## Rigid/IMC Conduit Fittings-Hazardous Location T&B Catalog Number:

**UPC Number:** GUAC14-TB  
**Status:** 78621034433  
**Description:** Active

1/2 in. GUAC Hazardous location Conduit Outlet Box, Box-Ductile Iron-Zinc Plated, Cover-Die Cast Aluminum, 6.8 cu.in.

### Features

All hubs have a minimum of five full threads and integral bushing  
 All boxes are furnished with internal grounding screw.

### Application

GUA boxes can be used for hazardous location conduit runs for the following: (1) Allows for mounting of fixture outlets when used with appropriate covers; (2) Provides easy access to wiring; (3) Provides junction in conduit for wire pulling and splices; (4) Changes direction in rigid conduit systems; (5) Attaches two or more pieces of conduit long runs; (6) Guards against damage to wires in rigid conduit.

### General

**Material:** Ductile Iron  
**Finish:** Zinc Plated  
**Volume (cu.in.):** 6.8

### Dimension Information

**Hub Size (inches):** 1/2  
**Dimension A (inches):** 2 1/4  
**Dimension B (inches):** 2 1/2  
**Dimension C (inches):** 7/8  
**Throat Diameter-Max (inches):** 0.610  
**Throat Diameter-Min (inches):** 0.570

### Specifications

**3dmodel:** Available on Website

### Packaging

**Package in Units:** 1  
**T&B Sold in UOM:** Each  
**T&B Weight Per UOM:** 173.88 lbs. per 100

### Notes

**\*Note:** Class I, Div. 1&2, Groups C, D - Explosionproof  
**\*\*Note:** Class II, Div. 1, Groups E, F, G - Dust-Ignitionproof  
**\*\*\*Note:** Class III, Div. 1&2 - Raintight  
**\*\*\*\*Note:** NEMA 3, 4, 7 CD, 9 EFG - Wet Locations

### Certifications

**RoHS Compliance:** Yes

## Certifications



File Nbr:  
E 202368

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)