

Sets / sets

PMS SKS



4 mm System / 4 mm system

Produktbeschreibung	Product description		
Beschreibung	Description	<p>Prüfmittelset Standard für 4 mm System.</p> <ul style="list-style-type: none"> • KLEPS 30 Klemmprüfspitze mit drehbarer Drahtzange und flexiblem Schaft zum Abgreifen von Pins und Drähten bis ø 4mm. • AK 2 S Isolierte Abgreifklemme zum Anklemmen von feinsten Drähten, Klemmbereich bis max. 9,5 mm Bolzendurchmesser. • PRUEF 2 Prüfspitze mit schlanker Edelstahlspitze zum Durchstoßen von Isolier-/ Oxidschichten. • MLN x/1 Messleitung mit beidseitig 4 mm Stecker sowie 4 mm Buchse für Turmsteckbauweise. (Längen 50cm, 100cm, 200cm) <p>Weitere technische Details entnehmen Sie bitte den einzelnen Produktdatenblättern.</p>	<p>Test equipment set Standard for 4 mm system.</p> <ul style="list-style-type: none"> • KLEPS 30 Clamp-type test probe with rotating grip jaws and flexible shaft for clamping of pins and wires up to ø 4 mm. • AK 2 S Insulated alligator clip for clamping of finest wires, clamping range up to a maximum of 9.5 mm bolt diameter. • PRUEF 2 Test probe with slender stainless steel tip for penetration of insulation and oxide layers. • MLN x/1 Measuring lead with 4 mm plug and 4 mm socket for tower construction on both sides. (length: 50 cm, 100 cm, 200 cm) <p>Please find further technical details on individual product data sheets.</p>
Lieferumfang	Delivery	<ul style="list-style-type: none"> • 1x Messlfg. MLN 50/1 schwarz (934 060-100) • 1x Messlfg. MLN 50/1 rot (934 060-101) • 2x Messlfg. MLN 100/1 schwarz (934 062-100) • 2x Messlfg. MLN 100/1 rot (934 062-101) • 1x Messleitung MLN 200/1 schwarz (934 065-100) • 1x Messleitung MLN 200/1 rot (934 065-101) • 1x Klemmprüfspitze KLEPS 30 schwarz (930 113-100) • 1x Klemmprüfspitze KLEPS 30 rot (930 113-101) • 1x Abgreifklemme AK 2 S schwarz (932 146-100) • 1x Abgreifklemme AK 2 S rot (932 146-101) • 1x Prüfspitze PRUEF 2 schwarz (973 368-100) • 1x Prüfspitze PRUEF 2 rot (973 368-101) 	<ul style="list-style-type: none"> • 1x test lead MLN 50/1 black (934 060-100) • 1x test lead MLN 50/1 red (934 060-101) • 2x test lead MLN 100/1 black (934 062-100) • 2x test lead MLN 100/1 red (934 062-101) • 1x test lead MLN 200/1 black (934 065-100) • 1x test lead MLN 200/1 red (934 065-101) • 1x clamp-type test probe KLEPS 30 black (930 113-100) • 1 x clamp-type test probe KLEPS 30 red (930 113-101) • 1 x alligator clip AK 2 S black (932 146-100) • 1 x alligator clip AK 2 S red (932 146-101) • 1 x test probe PRUEF 2 black (973 368-100) • 1 x test probe PRUEF 2 red (973 368-101)
Typ	Type	PMS SKS	PMS SKS
Artikel-Nr.	Article-no.	932 794-001	932 794-001