



Electronics

a vital part of your world

Find Answers:

Saturday, 19 November, 2005

CATALOG

Cross Reference

- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

Home

e-bulletin newsletter
SUBSCRIBE NOW!
 click here

Relays

↳ Industrial Relays (General Purpose)

MIDTEX 157-23Q200

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> General Info Sales Info 	<ul style="list-style-type: none"> Pricing Product Availability 	

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

Searchable Features:

Brand:	Midtex
RoHS/ELV Compliance:	Not reviewed for ELV/RoHS compliance
Lead Free Solder Processes:	Not reviewed for lead free solder process
Series:	157
Contact Arrangement:	3 Form C, 3PDT, 3 C/O
Contact Current Rating (Amps.):	10
Coil Magnetic System:	Monostable
Input Voltage (VAC):	24
Coil Suppression Diode:	Without
Coil Selection Criteria:	Nominal Voltage
Coil Resistance (Ω):	72
Actuating System:	AC

Other Properties:

Number of Bistable Coils:	Single
Comment:	Not recommended for new design.

Coil Power, Nominal (VA):	2.00
Coil Latching:	Without
Mounting Options:	Socket
Termination Type:	Solder/.187 Quick Connect Plug-in
Enclosure:	Flanged Dust Cover
Relay Type:	General
LED Indicator:	Without
Contact Material:	Silver Cadmium Oxide

[Copyright](#) and [Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]