


Photoluminescent Area Marking



Warning Tape: Standard Luminous Intensity



Size	Red/Photolum. Striped		Black/Photolum. Striped	
	Right	Left	Right	Left
15 mm x 12 m	263362	263363		
15 mm x 25 m	263364	263365		
30 mm x 12 m	263366	263367		
30 mm x 25 m	263368	263369		
60 mm x 12 m	263370	263371		
60 mm x 25 m	263372	263373		

Standard Package: 1 roll

ON REQUEST



Photoluminescent Warning Strips


Self-adhesive aluminium warning strips with a high luminous intensity.

Size	Red/Photolum. Striped		Black/Photolum. Striped	
	Right	Left	Right	Left
100 x 1.5 cm	251940		251934	
100 x 3 cm	251942		251936	
100 x 6 cm	251944		251938	

ON REQUEST

ON REQUEST

Standard Package:
1 strip



Green Arrow Tape in Standard Photoluminescent Quality



Standard Package:
1 roll

Size	Part No.
30 mm x 12 m	263374
30 mm x 25 m	263375
60 mm x 12 m	263376
60 mm x 25 m	263377

Green Arrow Strips in High Photoluminescent Quality



Standard Package:
1 strip

Size	Part No.
100 x 3 cm	251945
100 x 6 cm	251946

Photoluminescent Door Marking Tape



Standard Package:
1 roll

Size	Part No.
30 mm x 12 m	263378
30 mm x 25 m	263379
60 mm x 12 m	263380
60 mm x 25 m	263381

Photoluminescent Door Marking Strips



Standard Package:
1 strip

Size	Part No.
100 x 3 cm	251947
100 x 6 cm	251948


Photoluminescent Anti-skid Strips

These self-adhesive aluminium anti-skid strips are ideal for marking the edges of stairs and doorways. They are available in a standard luminous intensity version and a high luminous intensity version.

Part No.	Description	Size
251925	Aluminium Standard intensity	80 x 3 cm
251926	Aluminium High intensity	80 x 3 cm
251927	Aluminium Standard intensity	80 x 5 cm
251928	Aluminium High intensity	80 x 5 cm
251929	Aluminium Standard intensity/Striped	80 x 3 cm
251930	Aluminium High intensity/Striped	80 x 3 cm
251931	Aluminium Standard intensity/Striped	80 x 5 cm
251932	Aluminium High intensity/Striped	80 x 5 cm

Standard Package:
1 strip





Anti-Skid Products

Roll-Mounted Anti-Skid Tape

Anti-Skid tape's high degree of friction helps to prevent slipping and falling on wet or slippery floors. Rugged Polyester is an adhesive backed plastic tape coated with thousands of particles of durable aluminium oxide grit.

- Bonds permanently to clean, dry floors.
- Works indoors or outdoors.
- Withstands grease and oil.
- Eliminates masking clean-up and drying time.

Length: 18 m

Standard Package: 1 roll



Colour	Width in mm				
	25	50	100	150	300
Black	078189	078190	078191	078193	078194
Yellow		078091	078092		
Brownish Red	078197	078198	078199		
White/grey		078187			
Clear		078188			
Fluorescent Yellow		078183			
Fluorescent Green		078182			
Fluorescent Orange		078184			

} only indoor use



Anti-Skid Tape-Die-Cut Cleats

Installation is easy, just peel off protective liner and press in place.

Material: Adhesive backed plastic cleat

Standard package: 50 cleats

Colour	Size mm.	Part No.
Black	19 x 600	078192
Black	150 x 600	078195
Black	140 x 140	078196
Red	140 x 140	078177



Reflective & Glow-in-the-Dark Die-Cut Cleats

Provides an extra margin of safety at night, during blackouts or in low light conditions.

Standard Package: 24 cleats

Description	Size mm.	Part No.
Reflective	150 x 600	078161
Glow-in-the-dark	150 x 600	078162

Anti-Skid Tape/Hazard Marking Die-Cut Cleats

The Anti-skid tape provides traction on slick floors, while the printed message signals a visual warning.

Standard Package: 24 cleats



Legend	Size	Part No.
Caution	15 cm x 60 cm	078160
Watch your step	15 cm x 60 cm	078163

Striped Anti-Skid Tape

This bright yellow and black striped Anti-Skid Tape aids visibility.

Material: Adhesive backed plastic tape, oxide grit coated.

Standard Package: 1 roll (18 m)

Colour: Black/Yellow


25 mm	50 mm	75 mm	100 mm	150 mm
078146	078147	078148	078149	078150



Edge Sealing Compound

Prevents tape edges from lifting in high traffic areas.

Part No.: 278100



Primary Glue

To be used on porous or irregular surfaces. Neoprene based this glue is particularly resistant to water, oil and grease.

Part No.: 278101

