

Handset & Coiled Cord

6 Conductor Modular Line Cord



6 conductor line cord with 6P6C RJ12 modular plugs on each end. Various lengths and color combinations are available to special order. Both straight-thru and cross-over wiring type are available. Austel CCL # printed on cord.

Austel Permit # C89/01A/0296

[BULK]

Cat #	Length	Wiring Polarity
W2472	Various	Either

RJ45/RJ45 Modular Line Cord



4 conductor line cord fitted with one 6 position RJ11 and one 8 position RJ45 modular plug. Various lengths, colors & wiring configurations are available to special order. Both straight-thru and cross-over wiring type are available. Austel CCL # printed on cord.

Austel Permit # C89/01A/0296

[BULK 300]

Cat #	Length	Wiring Polarity
W2478	2 Metre	Either
W2483	3 Metre	Either
W2485	5 Metre	Either
W2488	10 metre	Either
W2489	15 metre	Either

RJ45/RJ45 Modular Line Cord



Flat modular line cord with an 8P8C RJ45 modular plug on each end. Available with 4, 6 or 8 conductor cord in various lengths, colors & wiring configurations. Both straight-thru and cross-over wiring type are available. Austel CCL # printed on cord.

Austel Permit # C89/01A/0296

[BULK]

Cat #	Length	Wiring Polarity
W2474	Various	Either

Modular Coiled Handset Cord



Standard 4 conductor coiled cord fitted with 4P4C U.S. modular plugs. Can also be supplied with any tail lengths, other connectors or unterminated if specified.

Austel Permit # C89/01A/0296

[BULK 200/300] [BLST 32/60]

Cat #	Color	Length
W3030	Ivory	3 Metre
W3040	Ash	3 Metre
W3010	Black	3 Metre
W3060	White	3 Metre
W3005	Grey	3 Metre
W3020	Brown	3 Metre
W3100	Ivory	5 Metre
W3110	Ash	5 Metre
W3080	Black	5 Metre
W3130	White	5 Metre
W3170	Ivory	8 Metre
W3180	Ash	8 Metre
W3150	Black	8 Metre
W3200	White	8 Metre

6 and 8 Conductor Coiled Cord



Flat or round coiled 6 or 8 conductor cord fitted with U.S. modular plugs. Can be supplied with any tail lengths, other connectors or unterminated if specified.

[BULK]

Cat #	Color	Conductor	Flat/Round	Length
W3310	Black	6	Flat	3 Metre
W3320	Black	6	Flat	5 Metre
W3420	Black	8	Flat	3 Metre
W3330	Black	6	Round	3 Metre
W3333	Ash	6	Round	3 Metre
W3335	Black	6	Round	5 Metre
W3400	Ash	8	Round	3 Metre

Armoured Handset Cord



Flexible metal armoured 4 conductor handset cord. Vandal resistant for emergency and public telephones.

[BULK]

Cat #
K2958

Special Coiled Cords



Access Communications are experts in manufacture and supply of specialised flat or round coiled cords. Our standard conductors are tinsel but other conductor types are also available. Polyester or Kevlar threads can be added for extra strength if required. Ends can be made with any tail lengths, connectors or unterminated if specified.

[BULK]

Expandite & Block



6 conductor round coiled cord terminated with 6 contact terminal blocks. For security, cash drawers and other applications. Terminal blocks and coiled cord also available separately.

[BULK 20/120]

Cat #	Type
K5600	Complete
K5605	Block Only
W3333	Cord Only

Extension Reel 15M



Standard Australian telephone extension cord with 605 plug and 610 socket on a compact dispenser reel. Fitted with convenient carry handle for portability. Available in a full color or plain white gift box. ACA Supplier Code N692

[BOX]

Cat #	Length	Color
K3510	15M	Ivory