

KM6-II GUIDES

ONE PART GUIDES

- Type 1 PCB** For Eurocards of 1,6mm thickness, either 100mm, 160mm or 220mm long. Compatible with grounding clip, see page 35
- Type 2 PCB** For Eurocards of 2,4mm thickness, either 160mm or 220mm long. Not compatible with grounding clip.
- Type 3 PIU** Plug-in unit (piu) type for cards 111,76 or 245,1mm height, 1,6mm thickness, 160 or 220mm long.
- Type 4 PCB** For Eurocards of 1,6mm thickness, 220mm long, this guide will fit over intermediate extrusions, permitting mixing of pcb depths. Compatible with grounding clip. See page 36.

Contents of kit

Description	Material/Finish
Types 1, 3, 4	Luranyl 2452/1 or equivalent, green
Types 2	Luranyl 2452/1 or equivalent, black

Ordering information

Description: KM6-II Guides - One part

Type	Application	Board Length	Qty.	Order code
1	PCB 1,6mm thick	100 mm	10	950-242850
		160 mm	10	950-232662
		160 mm	1000	956-243239
		220 mm	10	950-232663
		220 mm	1000	956-243240
2	PCB 2,4mm thick	160 mm	10	173-232666
		220 mm	10	173-232667
3	Plug-in unit	160 mm	10	950-232664
		220 mm	10	950-232665
4	Low profile PCB	220 mm	10	950-232668

THREE PART GUIDES

- Type 5** Aluminium centre section, with plastic slide in guide section, for 280mm, 340mm or 400mm lengths, 1,6mm thickness. Order separately: End feet for pcb or piu.
- Type 6** Three part guide end feet for Eurocards of 1,6mm thickness.
- Type 8** Three part guide end feet for piu of 1,6mm thickness.

Contents of kit


Item/Description	Material/Finish
Type 5	Al extrusion, anodised, plastic side-in section
	Noryl 2452/1, black
Type 6 and 8	Noryl 2452/1, green

Luranyl 2452/1 is a UL94 V1 rated material with a continuous rating of 105°C


Ordering information

Description: KM6-II Guides - Three part

Type	Application	Board Length	Qty.	Order code
5	PCB 1,6mm thick	280 mm	10	950-276108
		340 mm	10	950-276109
		400 mm	10	950-276110
6	Guide feet, PCB 1,6mm thick		10 prs.	950-202635
8	Guide feet, PIU 1,6mm thick		10 prs.	950-202636




One part guides




One part guides


PCB Guides



Plug-in unit guides



Three part guides



Guide length 'L' Guides should be cut to pcb length minus 76mm.