

# Soldering Tip - 3/8"

**3/8" SERIES** 

COMPATIBLE STATIONS: Hexacon - 3/8" tip, American Beauty - 3/8" tip, Esico - 3/8" tip

Plato is one of the largest manufacturers of soldering tips in the world, producing tips to fit all of the most popular soldering stations. The long life and fast heat recovery of Plato soldering tips increases user effectiveness and decreases production times. All Plato soldering tips manufactured since January 2004 are tinned with Lead-Free solder.

Long Life: Using a high quality Plato soldering tip increases soldering speed and decreases the total cost of manufacture. Higher temperatures and high tin content solders, common in leadfree soldering processes, place additional strain on soldering iron tips. The long life of a Plato soldering iron tip reduces tip changes, decreasing the total number of tips used and decreasing

Rapid Heat Recovery: Plato soldering tips are constructed from highly conductive premium grade copper to transmit heat to the work more quickly than other brands of soldering tips. This quick heat recovery enables more joints to be soldered per minute, thus reducing manufacturing time and costs.



- · Fast heat recovering increases soldering speed
- Longer tip reduces manufacturing costs
- Fewer tip change overs

### **Product Dimensions**

# 66-409 Conical

1.6mm 10 units/case



# 66-201 Square

Cross Reference: American Beauty 43D, Hexacon HT566

1.6mm 10 units/case



#### 66-367 Screwdriver

Cross Reference: Hexacon 66-367, Hexacon HT129

4.8mm 10 units/case







### 66-627 Screwdriver

4.8mm 10 units/case




#### 66-300 Screwdriver

Cross Reference: American Beauty 823, Hexacon HT449 6.4mm 10 units/case



#### 66-349 Screwdriver

Cross Reference: Hexacon HT470 8.0mm 10 units/case



# 66-145 Chisel


Cross Reference: Hexacon HT151 9.5mm 10 units/case



# 66-704 Chisel

Cross Reference: American Beauty 43C 9.5mm 10 units/case









# **Environmental Policy**

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

# Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: <a href="www.techspray.com">www.techspray.com</a>.

North America Techspray P.O. Box 949 Amarillo, TX 79105 800-858-4043

Email: tsales@techspray.com

Europe
ITW Contamination Control
Saffierlaan 5
2132 VZ Hoofddorp
The Netherlands
+31 88 1307 400
Email: info@itw-cc.com

<u>Countries Outside US</u>
Call to locate a distributor in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

© 2013 Techspray, A Division of ITW

