



You are here: HARTING USA > Product Information > Product Lines > Han® Industrial Connectors > Han® Accessories > Han® Cable Entry Accessories

HAN® CABLE ENTRY ACCESSORIES

LOCK NUTS

73080255009	Lock Nut - M12 x 1.5 NPB		
73080255019	Lock Nut - M16 x 1.5 NPB		
73080255029	Lock Nut - M20 x 1.5 NPB	7300005304	Lock Nut - PG 13.5
73080255039	Lock Nut - M25 x 1.5 NPB	7300005305	Lock Nut - PG 16
73080255049	Lock Nut - M32 x 1.5 NPB	7300005306	Lock Nut - PG 21
73080255059	Lock Nut - M40 x 1.5 NPB	7300005307	Lock Nut - PG 29
73080255069	Lock Nut - M50 x 1.5 NPB		

ADAPTERS TO NPT (Metric to NPT and PG to NPT)

		7300005308	Adapter - PG11 to 3/8" NPT
7300005360	Adapter - M16 to 1/2" NPT	7300005310	Adapter - PG11 to 1/2" NPT
7300005322	Adapter - M20 to 1/2" NPT	7300005311	Adapter - PG13.5 to 1/2" NPT
7300005323	Adapter - M25 to 1/2" NPT	7300005312	Adapter - PG16 to 1/2" NPT
		7300005313	Adapter - PG21 to 1/2" NPT
7300005319	Adapter - M25 to 3/4" NPT	7300005314	Adapter - PG21 to 3/4" NPT
7300005324	Adapter - M32 to 3/4"NPT		
7300005320	Adapter - M32 to 1" NPT	7300005315	Adapter - PG29 to 1" NPT
7300005321	Adapter - M32 to 1 1/4" NPT	7300005316	Adapter - PG29 to 1 1/4" NPT
7300005325	Adapter - M40 to 1 1/4"NPT	7300005317	Adapter - PG36 to 1 1/4" NPT
		7300005318	Adapter - PG36 to 1 1/2" NPT
		730900005046	Adapter - PG42 to 1 1/2" NPT

ADAPTERS - Metric to PG and PG to Metric

Cable Entry Accessories

Adapters from M to NPT		
Male Thread	Female Thread	Part Number
M20	1/2"	73 00 000 5322
M25	1/2"	73 00 000 5323
M25	3/4"	73 00 000 5319
M32	3/4"	73 00 000 5324
M32	1"	73 00 000 5320
M32	1 1/4"	73 00 000 5321
M40	1 1/4"	73 00 000 5325

Adapters from M to PG		
Male Thread	Female Thread	Part Number
M20	PG11	73 00 000 5326
M25	PG16	73 00 000 5327
M25	PG21	73 00 000 5328
M32	PG29	73 00 000 5329
M40	PG29	73 00 000 5330
M50	PG36	73 00 000 5331
M50	PG42	73 00 000 5332

Adapters from PG to M		
Male Thread	Female Thread	Part Number
PG13.5	M20	73 00 000 5333
PG16	M20	73 00 000 5334
PG16	M25	73 00 000 5335
PG21	M25	73 00 000 5336
PG21	M32	73 00 000 5337
PG29	M40	73 00 000 5338
PG36	M50	73 00 000 5339

Adapters from PG to NPT		
Male Thread	Female Thread	Part Number
PG11	3/8"	73 00 000 5308
PG11	1/2"	73 00 000 5310
PG13.5	1/2"	73 00 000 5311
PG16	1/2"	73 00 000 5312
PG21	1/2"	73 00 000 5313
PG21	3/4"	73 00 000 5314
PG29	1"	73 00 000 5315
PG29	1 1/4"	73 00 000 5316
PG36	1 1/4"	73 00 000 5317
PG42	1 1/2"	73 00 000 5046

Increases - Metric		
Male Thread	Female Thread	Part Number
M20	M25	73 00 000 5340
M25	M32	73 00 000 5341
M32	M40	73 00 000 5342
M40	M50	73 00 000 5344
M50	M63	73 00 000 5345

Reducers - Metric		
Male Thread	Female Thread	Part Number
M25	M20	73 00 000 5346
M32	M25	73 00 000 5347
M40	M32	73 00 000 5348
M50	M40	73 00 000 5349

Metric Threaded Plugs	
Male thread	Part Number
M20	73 00 000 5350
M25	73 00 000 5351
M32	73 00 000 5352
M40	73 00 000 5353
M50	73 00 000 5354
M63	73 00 000 5355

NPT Hood and Housings

PG 11	convert to	3/8" NPT
PG 13.5	convert to	1/2" NPT
PG 16	convert to	1/2" NPT
PG 21	convert to	3/4" NPT
PG 29	convert to	1" NPT
PG 36	convert to	1 1/4" NPT

HARTING offers hoods and housings with the NPT adapters pre-installed. To change a PG Hood or Housing to an NPT thread, change the 5th digit to a "5". For example, 09 30 016 0520 (PG21) becomes 09 30 516 0520 (3/4" NPT). See the accompanying chart for conversion details.

"Han Key" PG/Metric Thread Gauge - P/N 98 49 950 0101

7300000092 1106

7300005326	Adapter - M20 to PG11	7300005333	Adapter - PG13.5 to M20
7300005327	Adapter - M25 to PG16	7300005334	Adapter - PG16 to M20
7300005328	Adapter - M25 to PG21	7300005335	Adapter - PG16 to M25
7300005329	Adapter - M32 to PG29	7300005336	Adapter - PG21 to M25
7300005330	Adapter - M40 to PG29	7300005337	Adapter - PG21 to M32
7300005331	Adapter - M50 to PG36	7300005338	Adapter - PG29 to M40
7300005332	Adapter - M50 to PG42	7300005339	Adapter - PG36 to M50

INCREASERS

7300005340	Increaser Metal - M20 to M25	0900005050	Increaser Metal - PG11 to PG13.5
7300005341	Increaser Metal - M25 to M32	0900005051	Increaser Metal - PG13.5 to PG16
7300005342	Increaser Metal - M32 to M40	0900005052	Increaser Metal - PG16 to PG21
7300005344	Increaser Metal - M40 to M50	0900005053	Increaser Metal - PG21 to PG29
7300005345	Increaser Metal - M50 to M63	0900005054	Increaser Metal - PG29 to PG36
		0900005055	Increaser Metal - PG36 to PG42
		0900005056	Increaser Metal - PG42 to PG48

REDUCERS

1900005060	Reducer - M20 to M16	0900005060	Reducer PG11 to PG7
7300005346	Reducer - M25 to M20	0900005061	Reducer PG11 to PG9
		0900005062	Reducer PG13.5 to PG9
1900005067	Reducer - M32 to M20	0900005063	Reducer PG13.5 to PG11
1900005068	Reducer - M32 to M25	0900005064	Reducer PG16 to PG13.5
7300005347	Reducer - M32 to M25	0900005065	Reducer PG21 to PG13.5
7300005348	Reducer - M40 to M32	0900005066	Reducer PG21 to PG16
7300005349	Reducer - M50 to M40	0900005067	Reducer PG29 to PG16
		0900005068	Reducer PG29 to PG21

PLUGS / BLANKING PIECES

1900005070	NPB Blanking Plug - M20	0900005070	NPB Blanking Plug - PG11
7300005350	NPB Blanking Plug - M20	0900005071	NPB Blanking Plug - PG13.5

19000005071	NPB Blanking Plug - M25	09000005072	NPB Blanking Plug - PG16
73000005351	NPB Blanking Plug - M25	09000005073	NPB Blanking Plug - PG21
19000005072	NPB Blanking Plug - M32	09000005074	NPB Blanking Plug - PG29
73000005352	NPB Blanking Plug - M32	09000005075	NPB Blanking Plug - PG36
19000005073	NPB Blanking Plug - M40		
73000005353	NPB Blanking Plug - M40		
73000005354	NPB Blanking Plug - M50		
73000005355	NPB Blanking Plug - M63		
19000005172	Plastic Blanking Plug - M32		
19000005173	Plastic Blanking Plug - M40		

HEX ADAPTERS - STANDOFFS

19360005134	Hex Adapter - M25	09360005131	Han U Hex Adaptor PG11
19360005135	Hex Adapter - M32	09360005132	Han U Hex Adaptor PG13.5
		09360005133	Han U Hex Adaptor PG16
		09360005134	Han U Hex Adaptor PG21
		09360005135	Han U Hex Adaptor PG29

HARTING Products

Applications
 Product Lines
 Value Added Solutions

Customer Service

Where to buy
 Terms & Conditions of Sales
 Download Center

About HARTING

Company Information

Contact

Contact us

Home