









RoHS Compliant



XC-235

ExpressCard PCle 1 Port RS232

"CONNECTIVITY CARDS ENGINEERED TO EXCEED EXPECTATIONS"



Features

- 1xRS232
- ExpressCard PCIe Implementation socket size
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software
- Lifetime Support
- Lifetime Warranty (registration required)

Options



XC-235: ExpressCard PCIe 1 Port

Description

ExpressCard providing one port RS232 where absolute compatibility with classic desktop serial COM ports is a necessity. ExpressCard is 34mm wide and fits 34mm or 54mm slots. Guaranteed low latency, memory mapped, no compromise high performance interface. Data transfer rates up to 921,600 baud rates and the 128 byte deep transmit and 128 byte receive FIFOS, coupled with 1Mbit/s line drivers deliver uncompromising performance on your laptop. Drivers for Windows 32 bit and 64 bit Operating Systems including Windows XP, Server 2003, Vista, Server 2008, Windows 7 and Windows 8.

This high performance range utilising PCIe native drivers. Excellent method of adding extra serial ports to your laptop.

Software

Microsoft signed drivers (easy installation & robust operation) for:

- Windows 8 32 bit & 64 bit Editions
- Windows 7 32 bit & 64 bit Editions
- Windows Vista 32 bit & 64 bit editions
- Windows XP 32 bit & 64 bit editions

As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.





















ORDER

Description

ExpressCard PCle 1 Port RS232

Code XC-235



ExpressCard PCle 1 Port R\$232

XC-235: Full Specification

Port	Ports	1
	Connector	DB9 Connector - 9 Pin Male
Pin 1 DCD Pin 2 RXD Pin 3 TXD Pin 4 DTR Pin 5 GND Pin 6 DSR Pin 7 RTS Pin 8 CTS Pin 9 RI		
General	PCB Layers	4
Control	Power Consumption	380mA @ 3.3V
	Weight	0.035 kg, 0.08 pounds
	Size	101(l) x 38(w) x 20(h) mm, 3.98(l) x 1.50(w) x 0.79(h) inchesmm
Interface	OS Compatibility	Microsoft Windows 8 32 bit & 64 bit Editions
PCI>>> EXPRESS		Microsoft Windows 7 32 bit & 64 bit Editions Windows Vista 32 bit & 64 bit Editions Windows XP 32 bit & 64 bit Editions
	BUS	ExpressCard PCIe Implementation
Approvals	Other Approvals	AEO (C-TPAT) Microsoft Certified Gold Partner WEEE RoHS
Windows Visitar Windows XP	Microsoft Approvals	Microsoft Certified Gold Partner Windows 7 32 bit & 64 bit Editions Windows Vista 32 bit & 64 bit editions Windows XP 32 bit & 64 bit editions
Box Content	Packaging	Installation CD including manual, Microsoft signed drivers & utilities
	Card	ExpressCard PCIe 1 Port RS232
Product Support	Warranty	Lifetime (online registration required)
	Support	Lifetime Web, Email and Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team
Additional	OEM option	Available for bulk buy OEM
Elektra O5 European Electronica Industry Naued	Made In	Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards "Manufacturer of the Year"
WINNER Manufacturer of the Year Made in the UK	Customisable	Brainboxes operate a "Perfect Fit Custom Design" policy for volume users. More Info: sales@brainboxes.com

Other PCI Express Cards: 1xRS232 | 2xRS232 | 4xRS232 | 8xRS232 | 1xRS422/485 | 2xRS422/485 | 4xRS422/485 Other Brainboxes Ranges: PCI | Bluetooth Serial Adapter | Ethernet to Serial Adapter | PCMCIA Serial Card | ExpressCard Serial Adapter | USB to Serial