



ShelfMax® Bins

6-inch tall shelf bins maximize storage capacity!

- Long-lasting, industrial-grade polymer bins offer superior design and construction
- The ShelfMax offers the longest lasting and best value for large capacity shelf bin storage

5 NEW! SIZES




ShelfMax Model No.	Outside Dimensions (In.)			Inside Dimensions (In.)			Capacity/Quantity		Accessories		
	L	W	H	L	W	H	Cubic Inches	Ctn. Qty.	Width Dividers*	Divider Pkg. Qty.	Card Stock
30040	11 $\frac{1}{2}$	4 $\frac{1}{2}$	6	9 $\frac{3}{4}$	2 $\frac{1}{2}$	5 $\frac{1}{16}$	175	16	40020 (7)	12	29301
30090	11 $\frac{1}{2}$	6 $\frac{1}{2}$	6	9 $\frac{3}{4}$	5	5 $\frac{1}{16}$	310	10	40030 (7)	12	29301
30080	11 $\frac{1}{2}$	8 $\frac{1}{2}$	6	9 $\frac{3}{4}$	6 $\frac{1}{2}$	5 $\frac{1}{16}$	398	8	40040 (7)	12	29301
NEW! 30010	11 $\frac{1}{2}$	11 $\frac{1}{2}$	6	9 $\frac{3}{4}$	9 $\frac{1}{2}$	5 $\frac{1}{16}$	591	8	40050 (7)	12	29301
30048	17 $\frac{7}{8}$	4 $\frac{1}{2}$	6	16	2 $\frac{1}{2}$	5 $\frac{1}{16}$	280	8	40020 (7)	12	29301
30098	17 $\frac{7}{8}$	6 $\frac{1}{2}$	6	16	5	5 $\frac{1}{16}$	505	10	40030 (7)	12	29301
30088	17 $\frac{7}{8}$	8 $\frac{1}{2}$	6	16	6 $\frac{1}{2}$	5 $\frac{1}{16}$	648	8	40040 (7)	12	29301
NEW! 30018	17 $\frac{7}{8}$	11 $\frac{1}{2}$	6	16	9 $\frac{1}{2}$	5 $\frac{1}{16}$	963	8	40050 (7)	12	29301
NEW! 30044	23 $\frac{3}{4}$	4 $\frac{1}{2}$	6	21 $\frac{3}{4}$	2 $\frac{1}{2}$	5 $\frac{1}{16}$	410	16	40020 (7)	12	29301
30094	23 $\frac{3}{4}$	6 $\frac{1}{2}$	6	21 $\frac{3}{4}$	5	5 $\frac{1}{16}$	686	10	40030 (7)	12	29301
NEW! 30084	23 $\frac{3}{4}$	8 $\frac{1}{2}$	6	21 $\frac{3}{4}$	6 $\frac{1}{2}$	5 $\frac{1}{16}$	935	6	40040 (7)	12	29301
NEW! 30014	23 $\frac{3}{4}$	11 $\frac{1}{2}$	6	21 $\frac{3}{4}$	9 $\frac{1}{2}$	5 $\frac{1}{16}$	1303	6	40050 (7)	12	29301

One color per carton. Specify Red, Blue, Yellow, Green, White or Clear. Order in carton quantities. * () = Max. # of dividers per bin.

COLORS

Red, Yellow, Blue, Green, White, Clear



ShelfMax® Bin Shelving & Pick Rack Systems

6" ShelfMax Wire Shelving Systems		Bin Dimensions (In.)			Shelf Dimensions (In.)			Quantity	
Model No.	Description	L	W	H	D	L	H	Bins	Shelves
AWS143630040	Wire Shelving w/ 30040	11½"	4½"	6"	14"	36"	74"	64	9
AWS143630090	Wire Shelving w/ 30090	11½"	6½"	6"	14"	36"	74"	40	9
AWS143630080	Wire Shelving w/ 30080	11½"	8½"	6"	14"	36"	74"	32	9
AWS143630010	Wire Shelving w/ 30010	11½"	11½"	6"	14"	36"	74"	24	9
AWS183630048	Wire Shelving w/ 30048	17½"	4½"	6"	18"	36"	74"	64	9
AWS183630098	Wire Shelving w/ 30098	17½"	6½"	6"	18"	36"	74"	40	9
AWS183630088	Wire Shelving w/ 30088	17½"	8½"	6"	18"	36"	74"	32	9
AWS183630018	Wire Shelving w/ 30018	17½"	11½"	6"	18"	36"	74"	24	9
AWS243630044	Wire Shelving w/ 30044	23½"	4½"	6"	24"	36"	74"	64	9
AWS243630094	Wire Shelving w/ 30094	23½"	6½"	6"	24"	36"	74"	40	9
AWS243630084	Wire Shelving w/ 30084	23½"	8½"	6"	24"	36"	74"	36½	9
AWS243630014	Wire Shelving w/ 30014	23½"	11½"	6"	24"	36"	74"	24	9

Bin color code: R=Red, B=Blue, Y=Yellow, G=Green, W=White, SC=Clear. Specify one bin color when ordering. #Bonus bins included.



AS1879048R

ShelfMax Steel Shelving Systems		Bin Dimensions (In.)			Shelf Dimensions (In.)			Quantity	
Model Number	Description	L	W	H	D	L	H	Bins	Shelves
AS1279040	12" Steel Shelving with 30040 Bins	11½"	4½"	6"	12"	36"	79"	80	11
AS1279090	12" Steel Shelving with 30090 Bins	11½"	6½"	6"	12"	36"	79"	50	11
AS1279080	12" Steel Shelving with 30080 Bins	11½"	8½"	6"	12"	36"	79"	40	11
AS1279010	12" Steel Shelving with 30010 Bins	11½"	11½"	6"	12"	36"	79"	32½	11
AS1879048	18" Steel Shelving with 30048 Bins	17½"	4½"	6"	18"	36"	79"	80	11
AS1879098	18" Steel Shelving with 30098 Bins	17½"	6½"	6"	18"	36"	79"	50	11
AS1879088	18" Steel Shelving with 30088 Bins	17½"	8½"	6"	18"	36"	79"	40	11
AS1879018	18" Steel Shelving with 30018 Bins	17½"	11½"	6"	18"	36"	79"	32½	11
AS2479044	24" Steel Shelving with 30044 Bins	23½"	4½"	6"	24"	36"	79"	80	11
AS2479094	24" Steel Shelving with 30094 Bins	23½"	6½"	6"	24"	36"	79"	50	11
AS2479084	24" Steel Shelving with 30084 Bins	23½"	8½"	6"	24"	36"	79"	42½	11
AS2479014	24" Steel Shelving with 30014 Bins	23½"	11½"	6"	24"	36"	79"	30	11

Bin color code: R=Red, B=Blue, Y=Yellow, G=Green, W=White, SC=Clear. Specify one bin color when ordering. #Bonus bins included.



APRD18AST00B

12" Deep Pick Rack Systems			Bin Dimensions (In.)			Bin Qty.
Model No.	Description	Bin Model No.	L	W	H	Bin Qty.
APRS040	Single-Sided Rack	30040	11½"	4½"	6"	64
APRS080	Single-Sided Rack	30080	11½"	8½"	6"	32
APRS090	Single-Sided Rack	30090	11½"	6½"	6"	40
APRS010	Single-Sided Rack	30010	11½"	11½"	6"	24
APRSAST00	Single-Sided Rack	30040 / 30090	See above			32 / 20
APRD040	Double-Sided Rack	30040	11½"	4½"	6"	128
APRD080	Double-Sided Rack	30080	11½"	8½"	6"	64
APRD090	Double-Sided Rack	30090	11½"	6½"	6"	80
APRD010	Double-Sided Rack	30010	11½"	11½"	6"	48
APRDAST00	Double-Sided Rack	30040 / 30090	See above			64 / 40

Bin color code: B=Blue, R=Red, Y=Yellow, G=Green, W=White, SC=Clear, GR=Gray, CRY=Crystal Clear. Specify color of bins when ordering. #Bonus bins included.

18" Deep Pick Rack Systems			Bin Dimensions (In.)			Bin Qty.
Model No.	Description	Bin Model No.	L	W	H	Bin Qty.
APRS18048	Single-Sided Rack	30048	17½"	4½"	6"	64
APRS18088	Single-Sided Rack	30088	17½"	8½"	6"	32
APRS18098	Single-Sided Rack	30098	17½"	6½"	6"	40
APRS18018	Single-Sided Rack	30018	17½"	11½"	6"	24
APRS18AST00	Single-Sided Rack	30048 / 30098	See above			32 / 20
APRD18048	Double-Sided Rack	30048	17½"	4½"	6"	128
APRD18088	Double-Sided Rack	30088	17½"	8½"	6"	64
APRD18098	Double-Sided Rack	30098	17½"	6½"	6"	80
APRD18018	Double-Sided Rack	30018	17½"	11½"	6"	48
APRD18AST00	Double-Sided Rack	30048 / 30098	See above			64 / 40

Bin color code: B=Blue, R=Red, Y=Yellow, G=Green, W=White, SC=Clear, GR=Gray, CRY=Crystal Clear. Specify color of bins when ordering. #Bonus bins included.

Bench Rack 12" D x 36½" W x 25" H			Bin Dimensions (In.)			Bin Qty.
Model No.	Description	Bin Model No.	L	W	H	Bin Qty.
APRBENCH040	Bench Pick Rack	30040	11½"	4½"	6"	24
APRBENCH090	Bench Pick Rack	30090	11½"	6½"	6"	15
APRBENCH010	Bench Pick Rack	30010	11½"	11½"	6"	16½

Bin color code: B=Blue, R=Red, Y=Yellow, G=Green, W=White, SC=Clear, GR=Gray, CRY=Crystal Clear. Specify color of bins when ordering. #Bonus bins included.



APRBENCH040G



1293 South Main Street, Akron, Ohio 44301 • Tel: 800.253.2467 • Fax: 330.761.6348 • sales@akro-mils.com
 In Canada: 8028 Torbram Road, Brampton, Ontario L6T 3T2 • Tel: 877.877.9680 • Fax: 905.791.4084 • sales@buckhorncanada.com
 Visit our website: akro-mils.com or akro-mils.com/canada.aspx