

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [130199-0030](#)  
**Status:** **Active**  
**Overview:** [MAX-LOC® Plus Shielded Cord Grip Assemblies](#)  
**Description:** Woodhead® MAX-LOC® Plus Shielded Cord-Grip Assembly, 1 AWG Cable with Red Silicone O-Ring and Grommet



Series

image - Reference only

**Documents:**  
[3D Model](#)  
[Drawing \(PDF\)](#)  
[Product Specification PS-130199-001 \(PDF\)](#)  
[Application Specification AS-130199-001 \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

| General        |                                                             |
|----------------|-------------------------------------------------------------|
| Product Family | Cable Grips                                                 |
| Series         | <a href="#">130199</a>                                      |
| Eye Type       | N/A                                                         |
| O-Ring         | Yes                                                         |
| Overview       | <a href="#">MAX-LOC® Plus Shielded Cord Grip Assemblies</a> |
| Product Name   | MAX-LOC®                                                    |
| Type           | MAX-LOC® Connector                                          |
| UPC            | 884982868465                                                |
| Woodhead       | Yes                                                         |

| Physical                   |                            |
|----------------------------|----------------------------|
| Approximate Break Strength | N/A                        |
| Bale Length                | N/A                        |
| Body Style                 | Straight                   |
| Cable Diameter             | 11.10-14.27mm (.437-.562") |
| Color - Grommet            | N/A                        |
| Gender                     | Female                     |
| Material - Body            | Aluminum                   |
| Material - Grip            | N/A                        |
| Mesh Length                | N/A                        |
| Number of Holes            | N/A                        |
| Thread Size                | N/A                        |

Material Info

| Reference - Drawing Numbers |               |
|-----------------------------|---------------|
| Application Specification   | AS-130199-001 |
| Product Specification       | PS-130199-001 |
| Sales Drawing               | SD-130199-001 |

**EU RoHS**  
**ELV and RoHS**  
**Compliant**  
**REACH SVHC**  
Not Reviewed  
**Low-Halogen Status**  
**Low-Halogen**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**  
[130199Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION