


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [73927-0411](#)
Status: **Active**
Overview: SFP+ and SFP Interconnect Solutions
Description: 1-by-4 Small Form-factor Pluggable (SFP) Ganged Cage, Elastomeric Gasket, Press-fit
Replacement Part Number: [74728-0420](#)

Documents:

[3D Model](#) [Test Summary TS-74728-0415 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Test Summary TS-73927-0002 \(PDF\)](#)



General

Product Family	I/O Connectors
Series	73927
Application	Module-to-Board
Comments	PCB Thickness: 1.60mm Single Sided Use & 3.00mm Belly-to-belly Use 4 Ports
Component Type	Cage Assembly
Overview	SFP+ and SFP Interconnect Solutions
Product Name	SFP
Replacement Part Number	74728-0420
Type	N/A
UPC	822348065127

Physical

Circuits (Loaded)	N/A
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Plating Mating	N/A
Net Weight	16.500/g
Orientation	Right Angle
PC Tail Length	3.05mm
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm, 3.00mm
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	4
Surface Mount Compatible (SMC)	No
Termination Interface: Style	Through Hole - Compliant Pin
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	N/A
Grounding to Panel	Yes
Shield Type	EMI Fingers, Full Shield
Shielded	Yes

Solder Process Data

Process Temperature max. C	70
----------------------------	----

Material Info

Reference - Drawing Numbers

EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[73927Series](#)

Use With

[74742 Cable Assemblies](#). [74743 Cable Assemblies](#). [73929 Cable Assemblies](#). [74720 SFP Adapter](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Insertion Tool for 1 by 4 Small Form-Factor Pluggable	0622029780
Removal Tool for 1 by 4 Small Form-Factor Pluggable	0622029790

This document was generated on 11/19/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION