

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

39-00-0377

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 254 Crimp Terminal, 22-28 AWG, 0.35µm Gold (Au), Nickel (Ni) Under-Plate, Brass, Loose



Series

image - Reference only

Documents:

- [Drawing \(PDF\)](#)
- [Product Specification PS-2759-003 \(PDF\)](#)
- [Product Specification PS-2759-004 \(PDF\)](#)
- [Product Specification PS-5045-003 \(PDF\)](#)
- [Product Specification PS-5045-004 \(PDF\)](#)
- [Product Specification PS-5046-004 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	2759
Application	Signal
Crimp Quality Equipment	Yes
Overview	KK® Interconnect System - Molex
Product Name	KK® 254
UPC	800753336490

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	64.000/mg
Packaging Type	Bag
Plating min - Mating	0.356µm
Plating min - Termination	2.032µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.2-1.7mm max.
Wire Size AWG	22, 24, 26, 28
Wire Size mm²	N/A

Material Info

Old Part Number	2759GL
-----------------	--------

Reference - Drawing Numbers

Product Specification	PS-2759-003, PS-2759-004, PS-5045-003, PS-5045-004, PS-5046-004
Sales Drawing	E-2759*, SD-2759*

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

2759Series

Use With

2695 , 5051

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool	0011030022
Insertion Tool	0638120000
Hand Crimp Tool	0638118200

Japan

Description	Product #
Hand Crimp Tool	0011260009
JHTR2262A	
Hand Crimp Tool	0011260025
JHTR2262J	

This document was generated on 04/07/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION