

"F" COAX ADAPTERS

Connec



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6



Fig. 7



Fig. 8



Fig. 9



Fig. 10



Fig. 11



Fig. 12



Fig. 13



Fig. 15



Fig. 16



Fig. 18



Fig. 19



Fig. 20



Fig. 21



Fig. 22

"F" Coax Adapters

Retail Part No.	Bulk Part Number	Figure Number	Description	Quantity/ Retail Pack
33-1566	33-1566-BU	1	"F" Female to RCA Female	1
32-3006	32-3006-BU	2	"F" Female to Female, with Nut and Washer	5
32-3706	32-3706-BU	2	"F" Female Inline Splice with Nut and Washer, Gold	5
32-3007	32-3007-BU	3	"F" Double Male Coupler, Knurled	2
32-3100	32-3100-BU	4	"F" Female to Push-On "F" Male	2
32-3700	32-3700-BU	4	"F" Female to Push-on "F" Male, Gold	1
	32-3101-BU	5	"F" Female UHF (PL-259) Male	
32-3102	32-3102-BU	6	"F" Female to RCA Male	1
32-3103	32-3103-BU	7	"F" Female to 3.5mm Male	1
32-3104	32-3104-BU	8	"F" Female to BNC Male	1
32-3105	32-3105-BU	9	Right Angle "F" Quick Male to Female	1
32-3108	32-3108-BU	10	"F" Male to RCA Female	1
32-3110	32-3110-BU	11	Right Angle Connector "F" Male to Female	1
32-3114	32-3114-BU	12	"F" Male to UHF Female	1
32-3120	32-3120-BU	13	"F" Male to BNC Female	1
32-3129	32-3129-BU	14	"F" Female to "G" Plug	1
32-3174	32-3174-BU	15	"F" Female to Pal Male	2
32-3180		16	"F" Voltage Blocking Coupler	1
	32-3184-BU	17	Right Angle "F" Female to "F" Female	
	32-3999-BU	18	"F" Female to Female	
	32-4000-BU	19	"F" Male to Pal Female	
	32-4001-BU	20	"F" Female to Pal Female	
	32-4003-BU	21	"F" Female to BNC Female	
32-436	32-436-BU	22	"F" Terminator 75 Ohm 1/2 Watt @5%	5

"F" COAX CONNECTORS



Fig. 1



Fig. 2



Fig. 6



Fig. 3



Fig. 7



Fig. 4



Fig. 8

"F" Male 1-Piece Compression 2-GHz Rated

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page	Cable Type	Qty. retail Package
	32-441-BU	32-441-100	1	Professional Quality Connector for RSC, 1-Piece, Red Banded	394	RG-59	
	32-443-BU	32-443-100	1	Professional Quality Connector for RSC, 1-Piece, Yellow Banded	394	RG-6	
	32-444-BU	32-444-100	1	Professional Quality Connector for RSC, 1-Piece, Blue Banded	394	RG-6, Quad Shield	
		32-447-100	2	360° Taper Seal 2GHz, Watertight, Low RFI	394	RG-6	

"F" Male 1-Piece 1/2" Crimp

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page	Cable Type	Qty. retail Package
32-440	32-440-BU	32-440-100	3	Male Crimp with Attached 1/2" Crimp, 2 Pack	394	RG-59 & RG-62	2
32-439	32-439-BU		3	Male Crimp with Attached 1/2" Crimp, 2 Pack	394	RG-6	2
	32-2990-BU		3	Male Crimp with Attached 1/2" Crimp	394	RG-6 Quad Shield	

"F" Male 1-Piece 1/2" Crimp-Brass

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page	Cable Type	Qty. retail Package
32-433			3	Male Crimp with Attached 1/2" Crimp-Brass, 2 Pack	394	RG-59 & RG-62	2
32-432	32-432-BU		3	Male Crimp with Attached 1/2" Crimp-Brass, 2 Pack	394	RG-6	2

Quad "F" Male 1-Piece 1/2" Crimp

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page	Cable Type	Qty. retail Package
	32-2991-BU		3	Male Crimp with Attached 1/2" Crimp-Quad Shield		RG-59 & RG-62	

Tri-shield "F" Male 1-Piece Crimp-Brass

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page	Cable Type	Qty. retail Package
	32-416-BU		3	Male Crimp with Attached 1/2" Crimp-Brass Tri-Shield		RG-6	

"F" Male 2-Piece Crimp-1/4" Ring

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page	Cable Type	Qty. retail Package
32-430	32-430-BU		4	"F" Male Crimp-on with Separate 1/4" Crimp Ring	394	RG-59 & RG-62	2
32-429	32-429-BU		4	"F" Male Crimp-on with Separate 1/4" Crimp Ring	394	RG-6	2
32-429-3	32-429-3BU		4	"F" Male Crimp-on with Separate 1/4" Crimp Ring Gold	394	RG-6	2

"F" Female Mounts

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page	Cable Type	Qty. retail Package
	32-466-BU		6	"F" Chassis Mount with Nut and Washer			
32-465	32-465-BU		7	PC Board Mount, 2-Pack			2
	32-467-BU		8	Right Angle PCB Mount, 28mm			

"F" COAX CONNECTORS (Cont.)



Fig. 1



Fig. 2



Fig. 3



Fig. 5



Fig. 9



Fig. 10

"F" Male 1-Piece 1/8" Crimp-Attached

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page	Cable Type
32-3000	32-3000-BU		1	Male Crimp-on with Attached 1/8" Crimp, 2 Pack	394	RG-59 & RG-62

"F" Male 1-Piece 1/8" Crimp-Gold Attached

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page	Cable Type
32-3701	32-3701-BU		1	Male Crimp with Attached 1/8" Crimp-Gold	394	RG-59 & RG-62

"F" Male 1-Piece 1/4" Crimp-Attached

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page	Cable Type
	32-412-BU		1	Male Crimp-on with Attached 1/4" Crimp-Ring	394	RG-6

"F" Male Twist-on Crimpless

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page	Cable Type
	SD-447-BU		2	"F" Male Twist-on Connector, Crimpless	394	RG-6 Quad Shield
32-3002	32-3002-BU		3	"F" Male Twist-on Connector, Crimpless, 5 Pack	394	RG-59 & RG-62
32-3003	32-3003-BU		3	"F" Male Twist-on Connector, Crimpless, 5 Pack	394	RG-6

"F" Male Twist-on Crimpless-Gold

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page	Cable Type
32-3702	32-3702-BU		3	"F" Male Twist-on Connector, Crimpless-Gold, 5 Pack	394	RG-59 & RG-62

"F" Male Twist-on Push-on

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page	Cable Type
32-3202	32-3202-BU		5	"F" Male Twist-on Push-on Connector, 5 Pack	394	RG-59 & RG-62

"F" Male 2-Piece Permanent Compression

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use GC cables on page	Cable Type
	SD-446-BU		9	"F" Male 2-Piece Permanent Compression, Commercial, Weatherproof	394	RG-6

"F" Male Compression Locking Nut Only

Retail Part No.	Bulk Part No.	Bulk Part No. 100 Package	Figure No.	Description	Use With	
	SD-446-1BU		10	"F" Male Compression Locking Nut Only, Weatherproof	Any female "F" type connector	