

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [52271-1279](#)  
**Status:** **Active**  
**Overview:** [FFC-FPC \(SMT\)](#)  
**Description:** Easy-On™ Type FFC/FPC Connector, Right-Angle, Surface Mount, ZIF, Bottom Contact Style, 12 Circuits, Lead-Free, High Barrier Packaging

**Documents:**

|  |  |
|--|--|
| <a href="#">3D Model</a>                                 | <a href="#">Application Specification AS-52271-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                            | <a href="#">Packaging Specification SPK-52271-002 (PDF)</a>  |
| <a href="#">Product Specification PS-52271-053 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>         |

**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                |                               |
|----------------|-------------------------------|
| Product Family | FFC/FPC Connectors            |
| Series         | <a href="#">52271</a>         |
| Overview       | <a href="#">FFC-FPC (SMT)</a> |
| Product Name   | Easy-On™                      |
| UPC            | 822348148714                  |

**Physical**

|                                |                       |
|--------------------------------|-----------------------|
| Circuits (Loaded)              | 12                    |
| Color - Resin                  | Natural               |
| Contact Position               | Bottom                |
| Durability (mating cycles max) | 30                    |
| Entry Angle                    | 90° Angle             |
| Flammability                   | 94V-0                 |
| Mated Height                   | 3.00mm                |
| Material - Metal               | Phosphor Bronze       |
| Material - Plating Mating      | Tin-Bismuth           |
| Material - Plating Termination | Tin-Bismuth           |
| Material - Resin               | Nylon                 |
| Net Weight                     | 164.000/mg            |
| Number of Rows                 | 1                     |
| Orientation                    | Right Angle           |
| PCB Locator                    | No                    |
| PCB Retention                  | Yes                   |
| Packaging Type                 | Embossed Tape on Reel |
| Pitch - Mating Interface       | 1.00mm                |
| Pitch - Termination Interface  | 1.00mm                |
| Polarized to PCB               | Yes                   |
| Stackable                      | No                    |
| Temperature Range - Operating  | -40°C to +85°C        |
| Termination Interface: Style   | Surface Mount         |
| Wire/Cable Type                | FFC/FPC               |


**Electrical**

|                               |                 |
|-------------------------------|-----------------|
| Current - Maximum per Contact | 0.5A            |
| Voltage - Maximum             | 50V AC (RMS)/DC |

**Material Info**

**Reference - Drawing Numbers**

|                           |               |
|---------------------------|---------------|
| Application Specification | AS-52271-001  |
| Packaging Specification   | SPK-52271-002 |



**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Not Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[52271Series](#)

**Mates With**

[http://www.molex.com/product/premoflex\\_ffc-fpc.html](http://www.molex.com/product/premoflex_ffc-fpc.html)>Molex Premo-Flex FFC</a>. Be sure to match like plating

Product Specification

PS-52271-053, RPS-52271-066, RPS-52271-067,  
RPS-52271-069, RPS-52271-070, RPS-52271-072,  
RPS-52271-073, RPS-52271-075, RPS-52271-077,  
RPS-52271-080, RPS-52271-085, RPS-52271-087,  
RPS-52271-091, RPS-52271-097  
SD-52271-036, SD-52271-037

Sales Drawing

This document was generated on 12/18/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**