

USB 2.0 to HDMI Dual or Multi Monitor External Video Graphics Card Adapter, 128 MB SDRAM - 1920x1200,1080p

MODEL NUMBER: U244-001-HDMI-R



Description

Tripp Lite's U244-001-HDMI-R USB to HDMI Multi Monitor External Video Adapter allows you to connect an additional monitor or HDTV to a computer/laptop's USB 2.0 port. Up to six adapters can be used simultaneously, allowing the user to connect up to six additional monitors/TV's to a single computer. Once the installation is done, the computer screen appears on the add-on monitor(s) without the hassle of function keys to swap to a second monitor. Supports HD resolutions up to 1080p (60Hz). Windows and Intel Mac compatible.

Features

- Add an additional HDMI monitor or TV through a single USB 2.0 port
- Hot pluggable; add or remove a monitor without the need for a system reboot
- Compatible with Windows XP, Vista, 7, 8, and 8.1. Supports both 32- and 64-bit.
- Supports Surface tablets running non-RT Windows 8 and 8.1
- Compatible with Intel Mac OS X 10.8 (10.8.3 and later), 10.9 and 10.10 (Mac OS X 10.9 and 10.10 is limited to a single add-on monitor. See driver Release Notes for details) Supports both 32- and 64-bit.
- Use up to six adapters simultaneously, adding up to six additional monitors to a single computer
- View large spreadsheets across multiple screens by extending video amongst all monitors
- Play video on one monitor while working on another
- Do multiple screen presentations from a laptop computer
- Bus powered...no external power adapter needed
- Features 128MB DDR SDRAM of memory
- Supports HD resolutions up to 1080p (60Hz)
- Uses DisplayLink DL165 chipset

Specifications

Highlights

- Connect a PC or Laptop to an HDTV with HDMI
- Windows and Intel Mac compatible
- Features 128MB DDR SDRAM of memory
- Supports HD resolutions up to 1080p (60Hz)

Applications

Office workstation

- View large spreadsheets across multiple screens
- Multitask more effectively without overlapping windows
- Edit on one screen while surfing the Internet for information on the other

On the road

- Do multiple screen presentations without bringing another computer
- Easily provide multiple screen exhibitions in a trade show

Graphics workstation

- Use second display for palettes/tools
- Get a panoramic view of large documents

Editing workstation

- Type documents on one screen while viewing reference material on the other
- Compare two documents simultaneously across two screens

Financial analysis

- Have one monitor per data stream
- View charts and live data at the



OVERVIEW	
Display Style	Adapter
Cable Type	USB
CONNECTIONS	
Connector A	USB A (MALE)
Connector B	HDMI (FEMALE)
SPECIAL FEATURES	
Chromebook Compatible	No
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>

same time

Entertainment

- View videos/TV on one screen and reviews on the other
- Get additional perspectives when playing games

System Requirements

- USB 2.0 port
- HDMI monitor or TV
- Compatible with Windows XP, Vista, 7, 8, and 8.1. Supports both 32- and 64-bit.
- Supports Surface tablets running non-RT Windows 8 and 8.1
- Compatible with Intel Mac OS X 10.8 (10.8.3 and later), 10.9 and 10.10 (Mac OS X 10.9 and 10.10 is limited to a single add-on monitor. See driver Release Notes for details) Supports both 32- and 64-bit.
- Reference the owner's manual for system requirements when using multiple adapters or when using the add-on monitor for DVD playback.

Package Includes

- U244-001-HDMI-R USB to HDMI Multi Monitor External Video Adapter
- 3 ft. USB Cable
- Quick Start Guide
- Driver CD with Owner's Manual