

Wiha Adjustable TorqueControl Tool Sets In Durable Storage Box



With Certificate of Calibration




With Certificate of Calibration




28590 24 Piece TorqueVario-S Micro-Bit Set

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 21 Micro Bits, Micro Bit holder and Torque adjustment tool. Packed in a compact durable storage box.

Item No.		
28590	Slotted: 1.5, 2.0, 3.0, 4.0mm Phillips: #00, #0, #1	lbs.
	TORX®: T6, T7, T8, T9, T10, T15	1.33
	Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32	
	28504 - Handle Range 7.5 - 20 Inch lbs.	

28593 24 Piece TorqueVario-S Micro-Bit Set


Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 21 Micro Bits, Micro Bit holder and Torque adjustment tool. Packed in a compact durable storage box.

Item No.		
28593	Slotted: 1.5, 2.0, 3.0, 4.0mm Phillips: #00, #0, #1	lbs.
	TORX®: T6, T7, T8, T9, T10, T15	1.33
	Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32	
	28501 - Handle Range 15-80 Inch/oz (+/- 10%)	

53 Piece Set



With Certificate of Calibration




59 Piece Set

With Certificate of Calibration




28595 53 Piece TorqueVario-S Bit Set, In Storage Box

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 50 Insert bits, 1/4" Bit holder and Torque adjustment tool.

Item No.		
28595	Slotted: 4.5, 5.5, 6.5, 8.0mm	lbs.
	Phillips: #0, #1, #2, #3	2.85
	TORX®: T6, T7, T8, T9, T10, T15, T20, T25, T27, T30	
	Hex Inch: 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16"	
	Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm	
	Pozidriv: #0, #1, #2, #3	
	Torq Set: #4, #5, #6, #8	
	Square: #1, #2, #3	
	Triwing: #0, #1, #2, #3, #4	
	28506 - Handle Range 10 - 50 Inch lbs.	
	28581 - 1/4" Bit Holder	

28589 59 Piece TorqueVario-S Bit Set, In Storage Box

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes 3 ergonomic multi-component adjustable TorqueVario-S handles, 39 Insert bits, 15 Sockets, 1/4" Bit holder, 1/4" Hex to 1/4" Square adapter and Torque adjustment tool.

Item No.		
28589	Slotted: 4.5, 5.5, 6.5mm	lbs.
	Phillips: #0, #1, #2	2.58
	TORX®: T5, T6, T7, T8, T9, T10, T15, T20, T25, T30	
	Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	
	Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm	
	Pozidriv: #1, #2	
	Square: #1, #2, #3	
	Inch Sockets: 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 3/8"	
	Metric Sockets: 4.0, 4.5, 5.0, 5.5, 6.0, 7.0, 8.0mm	
	3 Handles: 15-80 Inch/oz., 5-10 & 10-50 Inch lbs.	
	1/4" Bit Holder & 1/4" Hex to 1/4" Square adapter	