



NP8



NP26I



SS7



HBL52CM22



HBL5206WO



HBL7423WO



## Wallplates, 1-Gang

Description	Color	Duplex Receptacles Catalog Number	Style Line® Receptacles Catalog Number	Single Receptacle Plate 1.40 in. (35.6) Dia. Catalog Number	
Nylon, smooth.	Almond	<b>NP8AL</b>	<b>NP26AL</b>	<b>NP7AL</b>	
	Black	<b>NP8BK</b>	<b>NP26BK</b>	<b>NP7BK</b>	
	Brown	<b>NP8</b>	<b>NP26</b>	<b>NP7</b>	
	Gray	<b>NP8GY</b>	<b>NP26GY</b>	<b>NP7GY</b>	
	Ivory	<b>NP8I</b>	<b>NP26I</b>	<b>NP7I</b>	
	Light Almond	<b>NP8LA</b>	<b>NP26LA</b>	<b>NP7LA</b>	
	Office White	<b>NP8OW</b>	<b>NP26OW</b>	<b>NP7OW</b>	
	Orange	<b>NP8OR</b>	-	-	
	Red	<b>NP8R</b>	<b>NP26R</b>	<b>NP7R</b>	
	White	<b>NP8W</b>	<b>NP26W</b>	<b>NP7W</b>	
	Stainless steel 302/304, .035 in. (0.9) horizontal brushed finish.		<b>SS8</b>	<b>SS26</b>	<b>SS7</b>
	Brass .04 in. (1.0), horizontal brushed finish.		<b>SB8</b>	<b>SB26</b>	<b>SB7</b>
Aluminum .05 in. (1.3), horizontal brushed finish.		<b>SA8</b>	-	<b>SA7</b>	

## Weatherproof Covers

Description	Duplex Receptacles Catalog Number	Single Receptacle Plate 1.40 in. (35.6) Dia. Catalog Number
RTP, gray, for FS/FD box mounting.	<b>HBL5221</b>	<b>HBL7423WO</b>
RTP, yellow, for FS/FD box mounting.	<b>HBL52CM21</b>	<b>HBL74CM23WO</b>
RTP, gray, for device mounting.	<b>HBL5222</b>	-
RTP, yellow, for device mounting.	<b>HBL52CM22</b>	-
Cast aluminum for FS/FD box mounting.	<b>HBL5206WO</b>	<b>HBL7420</b>
Cast aluminum for device mounting.	<b>HBL5205WO</b>	-

Note: All weatherproof plates are UL Listed for Wet Locations.  
Those with suffix WO are listed for use with cover open, all others with cover closed.  
RTP is an abbreviation for reinforced thermoplastic polyester.  
See section N for additional information on cover plates.