

Meets ANSI/ESD S20.20 and Packaging standard ANSI/ESD S541



FEATURES:

- Provides physical protection with conductive material providing reliable path-to-ground
- Includes steel wire frame for extra strength
- No tooling costs
- Easy assembly without the need for tape, glue, or staples
- Ships flat, knocked down
- Available options include: Lid manufactured from Plastek™, ESD Handles, Static Dissipative Foam bottom to provide ESD and shock protection, and Document Holders
- Made in United States of America



Made in the
United States of America

SPECIFICATIONS:

Properties

Properties	Typical Values
Resin Type:	Polypropylene
Conductive:	Permanently
Surface Resistance:	< 1 x 10 ⁵ ohms per ANSI/ESD S11.11 and ESD TR53
Humidity Independent:	Yes
Temperature Tolerance:	-17°F to +230°F
Melting Point:	324°F

Per Packaging standard ANSI/ESD S541 section 6.1 Inside an ESD Protected Area "Packaging used within an EPA (that satisfies the minimum requirements of ANSI/ESD S20.20) shall be: 1. Low charge generation. 2. Dissipative or conductive materials for intimate contact."

Unless specified tolerance is ± 10%

Part #	REF #	Box Size - L x W x D (IN)	Box Size - L x W x D (MM)	Lid
39300	CPS436-SS	17 x 13 x 6 3/4	432 x 330 x 171	39130
39301	CPS438-SS	17 x 13 x 8 3/4	432 x 330 x 222	39130
39302	CPS439-SS	17 x 13 x 10 3/4	432 x 330 x 273	39130
39303	CPS403-SS	17 x 13 x 12 5/8	432 x 330 x 321	39130
39304	CPS452-SS	18 3/8 x 12 3/8 x 12 3/4	467 x 314 x 324	39132
39306	CPS405-SS	18 3/8 x 12 3/8 x 18 3/4	467 x 314 x 476	39132
39307	CPS406-SS	18 5/8 x 15 x 5 7/8	473 x 381 x 149	39133
39308	CPS468-SS	18 5/8 x 15 x 8	473 x 381 x 203	39133
39309	CPS460-SS	18 5/8 x 15 x 10	473 x 381 x 254	39133
39312	CPS446-SS	22 7/8 x 12 7/8 x 6	581 x 327 x 152	39131
39313	CPS448-SS	22 7/8 x 12 7/8 x 8	581 x 327 x 203	39131
39314	CPS440-SS	22 7/8 x 12 7/8 x 10	581 x 327 x 254	39131

Built to Order Item List

39305	CPS457-SS	18 3/8 x 12 3/8 x 17 1/8	467 x 314 x 435	39132
39310	CPS462-SS	18 5/8 x 15 x 12	473 x 381 x 305	39133
39311	CPS464-SS	18 5/8 x 15 x 14	473 x 381 x 356	39133
39315	CPS404-SS	22 7/8 x 12 7/8 x 12 5/8	581 x 327 x 321	39131
39316	CPS445-SS	22 7/8 x 12 7/8 x 15 1/4	581 x 327 x 387	39131
39317	CPS408-SS	22 7/8 x 12 7/8 x 18 1/4	581 x 327 x 464	39131

Specifications and procedures are subject to change without notice.

Plastek™ Shipper Saver Storage Container

PROTEKTIVE PAK
13520 MONTE VISTA AVENUE, CHINO, CA 91710
PHONE (909) 627-2578
ProtektivePak.com

DRAWING NUMBER
39300

DATE
January
2014

PROTEKTIVE PAK