

## Fluke AC87 Heavy Duty Bus Bar Clip Set



### Features

- One pair (red, black) of flat, right angle design for connecting to bus bars
- Adjustable collar provides 2 ranges of jaw openings up to 30 mm
- CAT III 600 V, 5 A rating. UL listed
- One year warranty

### Models

#### Model (1)

Model Name	Description
Fluke AC87	Fluke AC87 Heavy Duty Bus Bar Clip Set

### Accessories

#### Compatible Products (33)

Model Name	Description
<b><u>Fluke 114</u></b>	Fluke 114 Digital Multimeter
<b><u>Fluke 115</u></b>	Fluke 115 Digital Multimeter
<b><u>Fluke 116</u></b>	Fluke 116 Digital Multimeter
<b><u>Fluke 117</u></b>	Fluke 117 Electrician's Digital Multimeter with Non-Contact Voltage
<b><u>Fluke 123</u></b>	Fluke 123 Industrial ScopeMeter○ Hand Held Oscilloscope
<b><u>Fluke 123/S</u></b>	Fluke 123/S Industrial ScopeMeter○ Hand Held Oscilloscope
<b><u>Fluke 124</u></b>	Fluke 124 Industrial ScopeMeter○ Hand Held Oscilloscope
<b><u>Fluke 124/S</u></b>	Fluke 124/S Industrial ScopeMeter○ Hand Held Oscilloscopes with SCC120 kit
<b><u>Fluke 175</u></b>	Fluke 175 True RMS Digital Multimeter
<b><u>Fluke 177</u></b>	Fluke 177 True RMS Digital Multimeter
<b><u>Fluke 179</u></b>	Fluke 179 True RMS Digital Multimeter
<b><u>Fluke 289</u></b>	Fluke 289 True-RMS Industrial Logging Multimeter

**Fluke 365** Fluke 365 Detachable Jaw True RMS AC/DC Clamp Meter

---

**Fluke 373** Fluke 373 True RMS AC Clamp Meter

---

**Fluke 374** Fluke 374 FC True-rms AC/DC Clamp Meter  
**FC**

---

**Fluke 375** Fluke 375 FC True-rms AC/DC Clamp Meter  
**FC**

---

**Fluke 376** Fluke 376 FC True-rms AC/DC Clamp Meter with iFlex<sup>o</sup>  
**FC**

---

**Fluke 381** Fluke 381 Remote Display True RMS AC/DC Clamp Meter with iFlex<sup>o</sup>

---

**Fluke 705** Fluke 705 Loop Calibrator

---

**Fluke 707** Fluke 707 Loop Calibrator with Quick Click Knob

---

**Fluke 707Ex** Fluke 707Ex Intrinsically Safe Loop Calibrator

---

**Fluke 709** Fluke 709 Precision Loop Calibrator

---

**Fluke 709H** Fluke 709H Precision Loop Calibrator with HART Communications / Diagnostics

---

**Fluke 712** Fluke 712 RTD Process Calibrator  
**RTD**

---

**Fluke 715** Fluke 715 Volt/mA Calibrator

---

**Fluke 724** Fluke 724 Temperature Calibrator

---

**Fluke 725** Fluke 725 Multifunction Process Calibrator

---

**Fluke 787** Fluke 787 ProcessMeter™

---

**Fluke 789** Fluke 789 ProcessMeter<sup>T</sup>

---

**Fluke 83V** Fluke 83V Average Responding Industrial Multimeter

---

**Fluke 87V** Fluke 87V Industrial Multimeter

---

**Fluke 902** Fluke 902 FC True-rms HVAC Clamp Meter  
**FC**

---

**Fluke 902** Fluke 902 True RMS HVAC Clamp Meter

---

