



iPad® & iPhone® Printing Made Easy Print From All Your iOS Devices To Your Office Printers!



xPrintServer® Office Edition is an easy-to-use, affordable 'plug-and-print' solution for Apple® iOS devices, enabling mobile printing from the native iOS print menu to virtually any printer throughout your enterprise.

Designed for the Demands of Fast-paced Business

The BYOD ("bring your own device") phenomenon has created havoc for IT managers. Rest easy with the xPrintServer mobile print solution. Ongoing support and management of users, devices, and printing solutions is effortless with the new professional-grade features and functionality:

- USB printer support / sharing (wired or wireless)
- Network printer support (wired or wireless)
- Remote Authentication / Active Directory
- Configuration Save / Restore
- Proxy Server Support
- Printer User Management / Advanced User Configuration

Set-Up is Automatic & Quick!

No software or apps to download and manage. No need to buy new printers. Simply open the box, plug in your xPrintServer anywhere on your network (LAN) via an Ethernet cable. Within seconds, the xPrintServer will auto-discover the printers on your network for iOS device printing.



xPrintServer Highlights:

- Print to virtually any printer - no need to buy new printers
- No apps or software to buy or load
- Easy to use / automatic discovery and set up of printers
- Print directly from the iOS native menu
- Supports more than 4,000 top brand printers
- Administrative & security settings via web interface
- USB printer(s) can be shared over your network*

Unlimited Number of iOS Devices, Unlimited Number of Printers!

That's right. One xPrintServer supports a virtually unlimited number of iPad® and iPhone® users, as well as a virtually unlimited number of printers simultaneously. With the xPrintServer from Lantronix, your mobile workforce will be printing in minutes.



Open it. Plug it in. Print.

(iPhone®, iPad® and printer not included)

xPrintServer Features

> xPrintServer ships with:

- (1) xPrintServer-Office Edition,
- (1) RJ45 Ethernet cable (3 ft.)
- Mounting bracket,
- (4) rubber feet,
- (1) universal power adapter (International),
- and (1) QuickStart Guide

> Supported iOS Devices:

- xPrintServer- Office Edition supports:
- iPad, iPhone & iPod Touch running iOS 4.2 or later

> Supported Browsers:

- The following browsers are supported:
- Microsoft Internet Explorer (version 8.0 or higher)
 - Firefox (version 7.0 or higher)
 - Safari (version 5.0 or higher)
 - Chrome (version 14.0 or higher)

> Supported Operating Systems:

- Win 7, Win XP
- Mac OS 10.7

> Supported Printers:

The xPrintServer supports USB printers and network-attached printers (wired and wireless) with one of the following protocols:

- JetDirect / AppSocket
- LPD
- IPP

The xPrintServer supports over thousands of printer models from leading manufacturers including:

- HP
- Toshiba
- Lexmark
- Xerox
- Minolta
- Brother
- Epson
- Canon
- Ricoh
- And many more

> Physical Interface:

- (1) 10/100 Ethernet port – RJ45 connector
- (1) 2.0 USB port (supports connection to USB hubs)
- (1) Factory reset button

> Physical Dimensions:

- Size: 4.50 x 2.34 x .91 in (L x W x H)
- Weight: .27 Kg/0.6 pounds (xPrintServer device + power supply)

> Environmental

- Operating Temp: 0°C to +55°C (32°F to 131°F)
- Storage Temp: -40°C to +70°C
- Relative Humidity: 0% to 40%, non-condensing

> Power

- Input 5 VDC, 1A
- Power Consumption: < 1 Watt

> Certifications:

- Emissions and Immunity:
 - FCC Part 15 Subpart B, Class B
 - Industry Canada ICES-003 Issue 4 February 2004, Class B
 - CISPR 22: 2005 + A1: 2005 + A2: 2006 Information Technology Equipment Class B
 - VCCI V-3/2010.04 Class B
 - AS/NZS CISPR 22: 2009 Class B
 - EN 55022: 2006 + A1:2007 Class B
 - EN 61000-3-2: 2006 + A1: 2009 + A2: 2009
 - EN 61000-3-3: 2008
 - EN 55024: 1998 +A1: 2001 +A2: 2003
 - EN 61000-4-2: 2009
 - EN 61000-4-3: 2006 + A1: 2008
 - EN 61000-4-4: 2004 + A1: 2010
 - EN 61000-4-5: 2006
 - EN 61000-4-6: 2009
 - EN 61000-4-8: 1994 + A1: 2001
 - EN 61000-4-11: 2004
- Safety:
 - UL/EN 60950-1

> Warranty:

- 2 year limited

Ordering Information

United States

Call: 800.422.7055
Email: sales@lantronix.com
Buy Online: <http://www.lantronix.com>
NASDAQ: LTRX

Europe

Call: +31 (0) 76.52.3.6.74 4
Email: EMEA@lantronix.com

Asia/Pacific

Call: +852.3428.2338
Email: asiapacific_sales@lantronix.com

Japan

Call: +81.3.6277.8802
Email: japan_sales@lantronix.com

China


Call: +86.021.6237.8868
Email: Shanghai@lantronix.com

> Part Number

XPS1002FC-01-S

> Description

xPrintServer-Office Edition USB port, 100-240VAC International power supply with regional adapters, RoHS



***Each xPrintServer supports unlimited iOS devices, multiple network printers and up-to 8 USB printers (USB hub required to connect more than 1 USB printer).**



xPrintServer® Family Feature Comparison

Key Features	xPrintServer Home	xPrintServer Office
USB Printers Supported	✓ (Up-to 8†)	✓ (Up-to 8†)
Network Printers Supported (Including wireless printers)	✓ (Up-to 2)	✓ (Unlimited‡)
USB Printer Sharing Over Network (for Mac & PCs)	✓	✓
Printer User Management		✓
10/100 Ethernet	✓	✓
Proxy Server/Port		✓
Firmware/Driver Loading via USB Port		✓
Configuration Save/Restore		✓
Remote Authentication Active Directory		✓

†USB Hub required - not included ‡Up-to 10 recommended for optimal performance

