

PRODUCT SPECIFICATION

Brand	C.K
Product Range	Ecotronic Pliers, Cutters & Strippers
Catalogue number	3883, 3884, 3885, 3886, 3887, 3888, 3889, 3890, 3891, 3892, 3893, 3894, 3895
Date	19/01/2015

Range Description A range of stamped Electronic pliers, cutters & strippers
Features • Special tool steel blade, hardened for long-term cutting performance • Electro-static discharging handles - dissipative 10⁸ • Contoured, dual component handle design for comfortable working • Black oxidised finish for corrosion resistance and reduced glare • Smooth-action return spring for convenience during repetitive work • Joint with durable stainless steel rivet" Cutters are sharp, with precision ground cutting edges and full flush cut



3883



3884



3885



3886



3887



3888

Pliers are made for the safe handling of small components in fine applications (e.g microelectronics and precision mechanics)



3889



3890



3891



3892

Strippers are suitable for stripping all common wire insulation types
Special tool steel blades, hardened for long-term performance
Integrated shears for cutting soft copper wires up to 3mm Ø / 8AWG Stranded



3893



3894



3895

Item Number	Item Description	EAN No	Commodity code	Carton Qty
T3883	C.K Ecotronic ESD Side Cutters (Micro)	5013969938838	82032000	10
T3884	C.K Ecotronic ESD Side Cutters (Micro, Reverse Cut)	5013969938845	82032000	10
T3885	C.K Ecotronic ESD Side Cutters (Slim)	5013969938852	82032000	10
T3886	C.K Ecotronic ESD Side Cutters (Slim, Relieved)	5013969938869	82032000	10
T3887	C.K Ecotronic ESD Side Cutters	5013969938876	82032000	10
T3888	C.K Ecotronic ESD Side Cutters (Relieved)	5013969938883	82032000	10
T3889	C.K Ecotronic ESD Long Snipe Nose Pliers	5013969938890	82032000	10
T3890	C.K Ecotronic ESD Short Snipe Nose Pliers	5013969938906	82032000	10

T3891	C.K Ecotronic ESD Flat Nose Pliers	5013969938913	82032000	10
T3892	C.K Ecotronic ESD Snipe Nose Pliers (Bent)	5013969938920	82032000	10
T3893	C.K Ecotronic ESD Wire Stripping Pliers (0.2 - 0.8mm Ø)	5013969938937	82032000	10
T3894	C.K Ecotronic ESD Wire Stripping Pliers (0.4 - 1.3mm Ø)	5013969938944	82032000	10
T3895	C.K Ecotronic ESD Wire Stripping Pliers (0.8 - 2.6mm Ø)	5013969938951	82032000	10

Technical product information	Cutting capacities (mm/AWG) – Soft Wire / Copper only T3883 0.2 - 1.3mm Ø T3884 0.2 - 1.3mm Ø T3885 0.2 - 1.3mm Ø T3886 0.2 - 1.3mm Ø T3887 0.2 - 1.6mm Ø T3888 0.2 - 1.6mm Ø
Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	These products do not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K Precision pliers and cutters are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered
Country of origin	Taiwan

Dimensional details

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3883			132	64	75	20	210	83
T3884			132	64	75	20	210	83
T3885			139	76	75	20	210	96
T3886			139	76	75	20	210	96
T3887			136	83	75	20	210	102

T3888			135	101	75	20	210	120
T3889			152	85	75	20	210	104
T3890			145	83	75	20	210	102
T3891			145	83	75	20	210	102
T3892			152	85	75	20	210	104
T3893			168	116	75	20	210	135
T3894			168	116	75	20	210	135
T3895			168	116	75	20	210	135