

## USB 3.0 SuperSpeed Laptop Dual Head Docking Station - HDMI and DVI Video, Audio, USB Hub Ports and Ethernet

MODEL NUMBER: U342-DHG-402



### Description

Tripp Lites U342-DHG-402, Universal USB 3.0 Laptop Docking Station, adds DVI, HDMI, Audio, Ethernet, and additional USB 3.0 and USB 2.0 ports to a laptop computer, all from a single device and over a single SuperSpeed USB 3.0 connection.

The universal docking station features two independent external monitor outputs (HDMI, DVI) that can be separately used to expand or mirror your computer's main desktop. Both HDMI and DVI outputs provided by the docking station supports video resolutions up to 1920x1200 .

An all-in-one solution, the universal laptop docking station combines USB 2.0 and USB 3.0 hubs, headphone and microphone audio connectors and a Gigabit Ethernet RJ45 port into a single docking station, making it the perfect accessory for enhancing laptop capability for users who need to connect and manage multiple devices at home or at the office.

### Features

- USB 3.0 is 10 times faster than USB 2.0 and supports data transfer rates of up to 5 Gbps
- Backward compatible with USB 2.0 and 1.1
- DVI-I and HDMI ports for connection of external monitors
- A VGA monitor can be connected to the DVI-I port using a DVI-to-VGA adapter, such as a Tripp Lite P556-Series ca
- A DVI monitor can be connected to the HDMI port using an HDMI-to-DVI adapter, such as a Tripp Lite P566-Series ca
- Supports video resolutions of up to 2048 x 1152
- Automatically resumes operation from hibernation and suspend modes
- Gigabit Ethernet port supports true 10/100/1000 Mbps network speeds
- IEEE 802.3az (Energy Efficient Ethernet) compliant
- Supports full duplex and half duplex operations

### Highlights

- Add multiple ports to your laptop via one USB 3.0 connection
- Backward compatible to USB 2.0 and 1.1
- Windows XP, Vista, 7, 8, and 8.1 compatible

### System Requirements

- Windows® XP (32-bit), Vista (32- and 64-bit), 7 (32- and 64-bit), 8 (32- and 64-bit) or 8.1 (32- and 64-bit)
- Available USB port (USB 3.0 required for USB 3.0 speeds)
- VGA\*, DVI or HDMI monitor
- 1.6 GHz Single Core processor (DVD playback on the add-on monitor requires a 2.0 GHz Dual Core processor)
- 1 GB RAM
- 30 MB of available disk space

(\* Requires a DVI-VGA adapter, such as Tripp Lite P556- Series cable )

### Package Includes

- U342-DHG-402
- External Power Supply (Input: 100-240V, 50/60 Hz, 0.8A Output: 5V, 4A) – 6 ft.
- USB 3.0 A/B Cable – 3 ft.
- Driver CD
- Owner's Manual



- Supports IPv4 and IPv6 pack Checksum Offload Engine (COE) to reduce CPU loading
- Supports Wake-on LAN, VLAN tagging and Auto-MDIX
- Two USB 3.0 and four USB 2.0 hub ports for connection of additional USB peripherals
- One USB 3.0 port supports USB Battery Charging (BC) specification 1.2, allowing it to provide 1.5 amps of power for faster charging of mobile devices
- 3.5 mm Mini Stereo jacks for connection of speaker and microphone
- Compatible with Windows® XP, Vista, 7, 8 and 8.1

## Specifications

OVERVIEW	
Dock Connectors	2 x USB3.0, 2 x 3.5mm Stereo, 4 x USB2.0, RJ45 LAN, DVI-I, HDMI
Cable Type	USB
PHYSICAL	
Shipping Dimensions (hwd / in.)	4.1 x 8.4 x 5.1
Shipping Dimensions (hwd / cm)	10.41 x 21.33 x 12.95
Shipping Weight (lbs.)	2.3
Shipping Weight (kg)	1.04
Unit Dimensions (hwd / in.)	7.4 x 1.2 x 3 (Base Is 2.8 x 5)
Unit Dimensions (hwd / cm)	18.8 x 3.05 x 7.62 (Base is 7.11)
Unit Weight (lbs.)	1.3
Unit Weight (kg)	0.59
Color	Black
CONNECTIONS	
Connector A	HARDWIRE
Connector B	HARDWIRE
SPECIAL FEATURES	
Chromebook Compatible	No
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>