

USB 3.0 SuperSpeed HDMI / VGA Mini Docking Station with Gigabit Ethernet

MODEL NUMBER: U342-SHG-001



Description

Tripp Lite's U342-SHG-001 is a compact, mini docking station that adds a HDMI or VGA video port, Gigabit Ethernet LAN port, and USB 3.0 port to your laptop, all through a single USB 3.0 connection. Built-in USB cable tucks away for easy transport. Ideal for laptop users who need the ability to use their laptop in a desktop environment, while maintaining the ability to quickly unplug and go. Bus powered...no external power adapter required. Backward compatible to USB 1.1 and 2.0 generations.

Features

- Add a monitor, USB 3.0 port, and Gigabit Ethernet to your laptop
- Portable design with built-in cable is perfect for travel, tucking into your laptop bag when not in use
- Bus Powered...no external power adapter required
- USB 3.0 is 10 times faster than USB 2.0, supporting data transfer rates up to 5 Gbps
- Backward compatible with USB 2.0 and 1.1
- Connect a DVI*, HDMI or VGA monitor or projector
- Supports video resolutions up to 2048 x 1152
- Automatically resumes from hibernation and suspend modes
- Gigabit Ethernet port supports true 10/100/1000 Mbps network speeds
- A USB 3.0 port is available for the connection of a USB peripheral device
- Compatible with Intel Mac OS X 10.8 (10.8.3 and later), 10.9 and 10.10 (Mac OS X 10.9 and 10.10 is limited to a single add-on monitor. See driver Release Notes for details) Supports both 32- and 64-bit.

* Requires an HDMI to DVI adapter, such as Tripp Lite's P566-Series cables

Specifications

Highlights

- Connect an external HDMI or VGA monitor to your laptop
- Adds a USB 3.0 and Gigabit Ethernet port to your laptop
- Compact design is perfect for travel, fitting easily into a laptop bag pocket

System Requirements

- Supports computers running Windows® XP, Vista, 7, 8, and 8.1
- Supports Surface™ tablets running non-RT Windows 8 or 8.1
- USB port (USB 3.0 port required for USB 3.0 speeds)
- DVI*, HDMI or VGA monitor
- Compatible with Intel Mac OS X 10.8 (10.8.3 and later), 10.9 and 10.10 (Mac OS X 10.9 and 10.10 is limited to a single add-on monitor. See driver Release Notes for details) Supports both 32- and 64-bit.

*Requires an HDMI to DVI adapter, such as Tripp Lite's P566-Series cables

Package Includes

- U342-SHG-001
- Driver CD
- Owner's Manual



OVERVIEW	
Dock Connectors	1 x USB3.0, 1 x HDMI, 1 x VGA, 1 x 10/100/1000 Ethernet RJ45
Cable Type	USB
OUTPUT	
USB Charging	No
INPUT	
Cable Length (ft.)	0
Cable Length (in.)	3
PHYSICAL	
Unit Dimensions (hwd / in.)	0.63 x 4.72 x 2.0
Unit Dimensions (hwd / cm)	1.6 x 11.99 x 5.08
Color	Black
CONNECTIONS	
Connector A	RJ45 (FEMALE)
Connector B	USB 3.0 A (FEMALE)
Connector C	HD15 (FEMALE)
Connector D	HDMI (FEMALE)
Included Cable (Side A)	USB 3.0 A-Male
SPECIAL FEATURES	
Chromebook Compatible	No
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>